

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

21415 North 15th Lane Suite 116 85027-0000, AZ Phoenix Phone: 480-681-0668

Fax: 480-681-0669



LED14ET8G4850 14W Led T8 48" 50K Type A 2050LM 80cri Ge By Current Lamps

LED14ET8G4850
Ge By Current Lamps
Linear Fluorescent Led Lamp, Non-Dimmable, Integrated Type; 48 Inch; UI, DLC Approval; Damp Location Application; 14 Watt Wattage; Led Tube; G13 Base Type; 50000 Life In Hour; T8 Shape Designation; 2050 Lumen Intensity; 5000; 80 Color Rendering Index
0.5380 (lbs/each)
Shape & Circular Lamps
2050 Lumen
LED Tube
14 Watt
G13
80 A
5000
48 INCH
Ballast Type Instant Start or Program Start
Led Linear Fluorescent Straight, U-Shape & Circular Lamps
14W LED T8 48" 50K TYPE A 2050LM 80CRI
NON-DIMMABLE, INTEGRATED TYPE; 48 INCH; UL, DLC APPROVAL; DAMP LOCATION APPLICATION; 14 WATT WATTAGE; LED TUBE; G13 BASE TYPE; 50000 LIFE IN HOUR; T8 SHAPE DESIGNATION; 2050 LUMEN INTENSITY; 5000; 80 COLOR RENDERING INDEX; BALLAST TYPE INSTANT START OR PROGRAM START
LINEAR FLUORESCENT LED LAMP, NON-DIMMABLE, INTEGRATED TYPE; 48 INCH; UL, DLC APPROVAL; DAMP LOCATION APPLICATION; 14 WATT WATTAGE; LED TUBE; G13 BASE TYPE; 50000 LIFE IN HOUR; T8 SHAPE DESIGNATION; 2050 LUMEN INTENSITY; 5000; 80 COLOR RENDERING INDEX
Linear Fluorescent Led Lamp



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

21415 North 15th Lane Suite 116 85027-0000, AZ Phoenix Phone: 480-681-0668

Fax: 480-681-0669

	-	•			
I	MAR	NI 1800	TILVAR	INTARK	MATIAN
ı۱	VIAI	111141	1111		114116111
	viui	ıuıu	tai Ci		nation

Brand	GE LIGHTING, INC./LAMPS
GTIN	10043168343005
Manufacturers Part Number	LED14ET8G4850
UPC	043168343008

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR	
	LAMPS	
Type	Non-Dimmable, Integrated	

Packaging

· J J		
Carton	1	
Package	20	
Weight Per each	0.538	

Uses, Certifications, and Standards

Application	Damp Location
Approval	UL, DLC