




# KT-LED15T8-48GC-850-D

T8 LED LAMP

### DESCRIPTION

15W T8 LED | 5000K | >83 CRI | High Efficiency





- Replacement for Conventional Fluorescent Lamp
- 50,000+ Hour Lifetime
- Approximately 40% More Energy Efficient that Standard F32T8 Lamps
- Environmentally Friendly: No Mercury Used
- Instant Startup
- Frosted Lens Eliminates Pixelation
- UL Classified













- Operating Temperature: -20°C/-4°F to 45°C/113°F
- Integral Driver (Isolated), Eliminates the Need for External Driver or Ballast
- 100+ Lumens per Watt
- Improved Lamp Durability with Shatterproof Coated Glass, designed to pass drop tests of 6' on hard surface
- ETL Sanitation Listed NSF/ANSI Standard 2 Food Equipment, Splash Zone (Not for Direct Food Zone without additional fixture considerations)

## **OPERATING SPECIFICATIONS**

### **ELECTRICAL CHARACTERISTICS**

Input Voltage	Power Consumption	Power Factor	Input Current
120-277Vac	15W	>0.9	0.16A @ 120V 0.07A @ 277V


#### RATED LIFE

L70 (Hours)	50.000


### PHOTOMETRIC CHARACTERISTICS

Color Temperature (CCT)	5000K	
Luminous Flux	1900 lm	
Color Rendering Index (CRI)	>83	
Efficacy	127 lm/W	
Beam Angle	240°	
Visible Light Area	325°	

# SPECTRAL DISTRIBUTION



## POLAR CANDELA DISTRIBUTION



Maximum Candela = 1248.55 Located at Horizontal Angle = 0, Vertical Angle 0

- 1. Violet Vertical Plane through Horizontal Angles (90-270)
- 2. Green Vertical Plane through Horizontal Angles (0-180)

Keystone Technologies • 1390 Welsh Road, North Wales, PA 19454 • Phone (800) 464-2680 • Fax (888) 966-0556 • www.keystonetech.com






# KT-LED15T8-48GC-850-D

T8 LED LAMP


#### WIRING DIAGRAMS

1. Cut all existing connections to ballast as shown below and remove ballast.

# **Typical Ballast Configurations:**



2. Re-wire fixture as shown below.





Connect wires directly to these terminals


# CAUTION: Use only non-shunted lampholders.

Do not install product in a fixture with shunted lampholders (found in all fixtures using instant start ballasts). If the current lampholders are shunted, remove them and replace them with non-shunted lampholders. Make new connections directly to terminals as indicated above.

Keystone can provide any style replacement lampholders. Call us at 800-464-2680.

### PHYSICAL CHARACTERISTICS

### LAMP DIMENSIONS



NOMINAL LENGTH: 48" BASE TYPE: G13 (Medium Bi-Pin)

### ORDERING INFORMATION

ORDER CODE	PACKAGING STYLE	PACK QTY.	ITEM STATUS
KT-LED15T8-48GC-850-D /G3-CP	Carton Pack (Egg Crate Packaging)	25	Quick Ship
KT-LED15T8-48GC-850-D /G3-DP	Distributor Pack (Individual Cartons)	12	Quick Ship

### CATALOG NUMBER BREAKDOWN

