



GE
Lighting

65541 - GE LED Candles

LED2CAM-IO-830/F

 Energy-efficient LED lamps. Long life.

Product Photo



GENERAL CHARACTERISTICS

Base Description	Medium Screw
Base Type	Screw-In
Lamp Type	Candle
Primary Application	Hand Lantern Post Light
Product Color	Clear
Product Technology	LED
Rated Life (Hours)	15000 h
Base	E26
Bulb Shape	Candles

PHOTOMETRIC CHARACTERISTICS

Lumens per Watt (Efficacy)	42 lm
Nominal Initial Lumen per Watt	42
Initial Lumens-nominal	100 lm
Color Rendering Index-CRI	80
Color Temperature	3000 K

PRODUCT INFORMATION

Product Code	65541
Description	LED2CAM-IO-830/F
Alternative Unit Of Measure	CASE

ELECTRICAL CHARACTERISTICS

Voltage <Nom>	120 V
Rated power (Watts)	2.4 W

CAUTIONS & WARNINGS

Caution

N/A

Not for use on dimming circuits. Not for use in totally enclosed fixtures. Do not open - no user serviceable parts inside. Not intended for use with emergency exit fixtures or emergency exit lights.

Warning

Risk of Electric Shock

Turn power off before inspection

installation or removal. Do not use where directly exposed to water. Not for use totally enclosed luminaires. For use with only approved Class 2 transformers/drivers.