

KT-LED43T8-96G-840-D T8 LED LAMP

DESCRIPTION

43W T8 LED | 4000K | >80 CRI | High Efficiency | 8 Foot



FYEAR	3
WARRANT	٦Y

Page 1 of 2

LAMP TYPE: Linear	COLOR TEMPERATURE: 4000K
BULB TYPE: T8 LED	COLOR RENDERING INDEX (CRI): >80
BASE TYPE: Fa8 (Single-Pin)	WARRANTY: 5 Years
WATTAGE: 43W	

PRODUCT FEATURES

- Replacement for Conventional T8/T12 8 Foot Single-Pin Fluorescent Lamp
- Double Ended Line Voltage Wiring: Connect power to each end for simplified installation
- 50,000+ Hour Lifetime
- Approximately 50% More Energy Efficient then Standard F96T12 Lamps
- Environmentally Friendly: No Mercury Used
- NSF Listed: NSF/ANSI Standard 2 Food Equipment, Splash Zone (Component level, Not for Direct Food Zone without additional fixture considerations)
- Includes 2 C-clips to be installed with the lamps into the fixture ballast cover to prevent any potential un-desired lamp twisting or sagging

- Frosted Lens Elimates Pixelation
- UL Classified
- Operating Temperature: -20°C/-4°F to 55°C/131°F
- Integral Driver (Isolated), Eliminates the Need
- for External Driver or Ballast
- 120+ Lumens per Watt
- DLC Listed
- Instant Startup

OPERATING SPECIFICATIONS

ELECTRICAL CHARACTERISTICS

Input Voltage	Power Consumption	Power Factor	Input Current
120-277Vac	43W	>0.9	0.36 @ 120V 0.16 @ 277V

RATED LIFE

L70 (Hours)



PHOTOMETRIC CHARACTERISTICS


Color Temperature	4000K
Luminous Flux	5500 lm
Color Rendering Index (CRI)	>80
Efficacy	128 lm/W
Beam Angle	325°

SPECTRAL DISTRIBUTION 3.50E-02 Flux (W/nm) 3.00E-02 2.50E-02 Ê 2.00E-02 ≚ 1.50E-02 1.00E-02 0.50E-03 0.00E-00 430 480 530 580 630 680 730 580 780 380

POLAR CANDELA DISTRIBUTION

936

Located at Horizontal Angle = 0, Vertical Angle 0



Keystone Technologies • 1390 Welsh Road, North Wales, PA 19454 • Phone (800) 464-2680 • Fax (888) 966-0556 • www.keystonetech.com

^{1.}Violet Vertical Plane through Horizontal Angles (90-270)

^{2.} Green Vertical Plane through Horizontal Angles (0-180)




Page 2 of 2


KT-LED43T8-96G-840-D T8 LED LAMP

WIRING DIAGRAMS

1. Identify ballast configuration as shown below and cut all wires connected to the ballast accordingly.




- 2. Confirm that the lampholders in the fixture are single-pin Fa8 lampholders. These DirectDrive LED tubes require single-pin Fa8 lampholders.
- 3. Rewire the fixture using existing lampholders as shown below according to the original ballast wiring configuration.



PHYSICAL CHARACTERISTICS

LAMP DIMENSIONS




NOMINAL LENGTH: 96" BASE TYPE: Fa8 (Single-Pin)

ORDERING INFORMATION

ORDER CODE	PACKAGING STYLE	PACK QTY.	ITEM STATUS
KT-LED43T8-96G-840-D-CP	Distributor Pack (Individual Cartons)	10	Quick Ship

CATALOG NUMBER BREAKDOWN



Keystone Technologies • 1390 Welsh Road, North Wales, PA 19454 • Phone (800) 464-2680 • Fax (888) 966-0556 • www.keystonetech.com