



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LHB12UNVL850CDU *Delisted* 87W Led High Bay 50K 12, 000LM 120/277V *Cooper Lighting Solutions*

Catalog Number	LHB12UNVL850CDU
Manufacturer	Cooper Lighting Solutions
Description	Led Linear High Bay, 12K Lumens, 5000K, 120/277V Dim Driver
Weight per unit	11.0 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.314 at 277V
Ballast Type	N/A
Lamp Type	LED
Number of Lamps	N/A
Socket Type	N/A
Voltage Rating	120/277V

Material, Color, and Finish

Style	(blank)
-------	---------

Descriptions

Description	*DELISTED* 87W LED HIGH BAY 50K 12,000LM 120/277V
extra long description	CLS LHB-12-UNV-L850-CD-U LINEAR HB,
Long Description	LED Linear High Bay, 12K Lumens, 5000K, 120/277V Dim Driver
Product Type	Linear HB, 12K Lumen, 120-277V, 5000K
Special Features	13 inch width in 2ft and 4ft lengths

Manufacturer Information

Brand	METALUX INDUSTRIAL
GTIN	00080083859184
Manufacturers Part Number	LHB-12-UNV-L850-CD-U
UPC	080083859184

Taxonomies, Classifications, and Categories

Category Description	LED HIGHBAY, LOWBAY & INDUSTRIAL LIGHTING
Type	INDUSTRIAL

Packaging

Carton	1
Weight Per each	11

Uses, Certifications, and Standards

Application	lighting
Mounting	Suspended