



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LT212100 2-1/2" Met L/T Non UI 100' *Southwire Company*

Catalog Number	LT212100
Manufacturer	Southwire Company
Description	TITAN2 Type Ef Is Manufactured With A Spiral Wound Interlocked Strip Of Corrosion-Resistant Galvanized Steel. A Flame Retardant Flexible PVC Jacket Is Extruded Over The Metal Core. The Gray Jacket Resists Oils Mild Acids and Exposure to Sunlight. Black Jacket Available But Subject to Economic Order Quantity. Reach/Rohs-2 (Chemical Limit) Compliant
Weight per unit	1.4 (lbs/ft)
Product Category	Liquid Tight Conduit

Descriptions

Description	2-1/2" MET L/T NON UL 100'
extra long description	SWC 55107304 Titan2 Type EF Extra-F
Long Description	Titan2 Type EF is manufactured with a spiral wound interlocked strip of corrosion-resistant galvanized steel. A flame retardant flexible PVC jacket is extruded over the metal core. The gray jacket resists oils mild acids and exposure to sunlight. Black jacket available but subject to economic order quantity. REACH/RoHS-2 (Chemical Limit) Compliant
Product Type	TITAN2 Type Ef Extra-Flexible Liquidtight Metal Conduit

Manufacturer Information

Brand	Flexible Conduit
GTIN	00032886063947
Manufacturers Part Number	55107304
UPC	032886063947

Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
----------------------	--------------

Packaging

Carton	100
Weight Per foot	1.37