



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LTC075 3/4" PVC Smooth NM LT Conduit

*Abb Installation Products, Inc*

Catalog Number	LTC075
Manufacturer	Abb Installation Products, Inc
Description	Industrial Grade, Type B Liquidtight Flexible PVC Conduit, 3/4 Inch Conduit Size, Approved For Outdoor and Direct Burial In The Us, UL Temperature Ratings - 105 Degrees C Dry, 60 Degree C Wet, 70 Degree C Oil, Csa Temperature Rating 18 to 75 Degrees C, Oil Resistant, Voltage Rating 600V, Black With Orange Markings
Weight per unit	0.2160 (lbs/each)
Product Category	Liquid Tight Fittings

### Features

Inside Diameter	0.81890
outside diameter	1.05120
Voltage Rating	600 V

### Material, Color, and Finish

Color	Black
-------	-------

### Dimensions and Weight

Length	1.20080
--------	---------

### Descriptions

Also Known As...	Carflex®
	Liquid Tight Conduit
Description	3/4" PVC SMOOTH NM LT CONDUIT
extra long description	ABB LTC075 3/4IN LT TYPE B COND PVC
Long Description	Industrial Grade, Type B Liquidtight Flexible PVC Conduit, 3/4 Inch Conduit Size, Approved for Outdoor and Direct Burial in the US, UL Temperature Ratings - 105 Degrees C Dry, 60 Degree C Wet, 70 Degree C Oil, CSA Temperature Rating 18 to 75 Degrees C, Oil Resistant, Voltage Rating 600V, Black with Orange Markings
Product Type	3/4IN LT Type B Cond PVC BLK
similar brands	Sealtite®
Special Features	The Smooth Inner Surface Ensures that Cables and Conductors Can Be Fed Through Very Easily

### Manufacturer Information

Brand	T&B Ind Fitting
GTIN	00786210789552
Manufacturers Part Number	LTC075
UPC	786210789552



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	NON-METALLIC SEALTITE AND FITTINGS
Type	Liquidtight Flexible Non-Metallic Conduit

## Trade Size

Trade Size	3/4 in
------------	--------

## Availability

minimum qty	100
-------------	-----

## Packaging

Carton	100
Weight Per foot	0.216

## Uses, Certifications, and Standards

Application	Machine Tools, Motor Hookups, Food Processing Equipment, Extensions from Wire Ways, and Sensor and Micro Switch Wiring Found In Control Consoles
standard	UL E95745, CSA