



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LU150MULTIKIT Magc Hid Bal *Sylvania-Ledvance*

Catalog Number	LU150MULTIKIT
Manufacturer	Sylvania-Ledvance
Description	OBS47335 120/208/240/277V Multi Tap Magnetic Core and Coil Ballast For 150W High Pressure Sodium Lamp
Weight per unit	8.0 (lbs/each)
Product Category	Lighting

Features

amperage rating	1.66/.96/.83/.72
ANSI Code	S55
Ballast Factor	1
Lamp Type	Metal Halide/S55
Minimum Starting Temperature	-40.000000000000000
Number of Lamps	1
Power Factor	>0.9
start type	Pulse
total harmonic distortion	<20
Voltage Rating	120, 208, 240, 277
Wattage	150

Dimensions and Weight

Height	3.850000000000000
Length	3.940000000000000
Width	2.810000000000000

Descriptions

Description	MAGC HID BAL
extra long description	SYL LU150/MULTI-KIT/47335 LU150MULT
Long Description	OBS47335 120/208/240/277V multi tap magnetic core and coil ballast for 150W high pressure sodium lamp
Product Type	LU150MULTIKIT 1/CS 1/Sku
Special Features	Multi Tap, Magnetic Core and Coil, High Voltage Pulse Present on Open Circuit, Ground Ballast Core and Metallic Case of Capacitor and Ignitor

Manufacturer Information

Brand	OSRAM
GTIN	00046135473357
Manufacturers Part Number	LU150/MULTI-KIT/47335
UPC	046135473357



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	UNIVERSAL BALLAST UNV
Type	Ballasts And Lighting Controls

Packaging

Carton	1
Weight Per each	8

Uses, Certifications, and Standards

standard	S55
----------	-----