

Eaton M22-DGH-R

Catalog Number: M22-DGH-R

Eaton 22.5 mm Modular Pushbutton Operator, RQM-Titan, Extended, Red Actuator, Silver bezel, Non-illuminated, 5,000,000 operations, Momentary, Guarded, M22 Series



General specifications

Product Name

Eaton M22 modular pushbutton

Catalog Number

M22-DGH-R

UPC

786685275147

Product Length/Depth

7 in

Product Height

1.5 in

Product Width

5 in

Product Weight

0.03 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

GoST-R

CE Marked

Bureau Veritas

Certifications

CCC Marked

CSA Certified

Lloyd's Register Certified

Catalog Notes

Includes contact block mounting adapter.

Type

Pushbutton

Bezel

Silver guarded

Actuator function

Momentary

Button color

Red

Actuator

Extended with guard, button

Illumination

Non-illuminated

Series

M22

Environmental rating

IP67, IP69K, NEMA 4X, NEMA 13

Operating cycles

5 million

Size

22.5 mm

Brochures[M22 Pilot Devices](#)**Catalogs**[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)**Drawings**[M22-DGH 2D Drawing Xchange](#)[M22-DGH AutoCAD 2D Footprint](#)[M22-DGH AutoCAD 2D Footprint \(mm\)](#)[M22-DGH 3D Model Xchange](#)[M22-DGH 2D PDF](#)[M22-DGH 3D Inventor](#)**Installation instructions**[M22 Operators and Accessories](#)**Specifications and datasheets**[Eaton Specification Sheet - M22-DGH-R](#)[Quick Selector - M22 Pushbuttons](#)[Global Data Sheet - M22-DGH-R](#)