

Eaton MBE2040B200BS

Catalog Number: MBE2040B200BS

Eaton Meter Breaker EUSERC Type BR , CSR2200 main breaker, 200A, 120/240V, Ring, 20 spaces, 40 circuits, 10 kAIC, Surface mounting, Box size B, Aluminum bus, Underground feed, Four-jaws, 1 socket, #6-250 kcmil line, #6-250 kcmil ground

General specifications

Product Name	Catalog Number
Eaton meter breaker EUSERC	MBE2040B200BS
UPC	Product Length/Depth
782114849118	5.38 in
Product Height	Product Width
43.38 in	14.44 in
Product Weight	Warranty
51 lb	10 year
Compliances	Certifications
EUSERC Approved	UL Listed



Product specifications

Interrupt rating

10 kAIC

Utility approvals

AZ : Arizona Public Service Company

ID : Idaho Power

OR : Idaho Power

WA : Seattle City Light

AK : Anchorage Municipal Light & Power

NV : NV Energy

CA : Pacific Gas and Electric (PG&E)

CA : Sacramento Municipal Utility District (SMUD)

AZ : Salt River Project (SRP)

MT : NorthWestern Energy

NE : NorthWestern Energy

SD : NorthWestern Energy

WY : NorthWestern Energy

WA : Puget Sound Energy

WA : Tacoma Public Utilities

Phase

Single-phase

Ground

#6-250 kcmil

Bus material

Aluminum

Number of jaws

Four-jaw

Main circuit breaker

CSR2200

Enclosure

NEMA 3R

Type

All-in-ones

Feed type

Bottom

Number of sockets

1

Used with

Type BR breakers

Resources

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - METER BREAKER WEST COAST STYLE

Specifications and datasheets

Eaton Specification Sheet - MBE2040B200BS

Technical Data Residential Meter Breakers: Type CH and BR Residential

Voltage rating

120/240 V

Number of circuits

40

Box size

B



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia