


# MC Lite® Metal Clad Aluminum Armored Cable 10 AWG

## Type MC (120/208V Colors & 277/480V Colors) Technical Specifications



**Armor**  
Interlocked Aluminum Strip

**Conductors**  
Solid or Stranded Copper

**Conductor Insulation**  
THHN/THWN

**Assembly Covering**  
Polypropylene Tape

**Maximum Temperature Rating**  
90°C (Dry)

**Grounding**  
Insulating Green Grounding Conductor

**Neutral Conductor**  
White 120/208V  
Gray 277/480V

**Maximum Voltage Rating**  
600V

**References & Ratings**

- UL 83, 1479, 1569, 1581, 2556, File Reference E80042
- NEC® 230.43, 300.22(C), 392, 396, 330, 501, 502, 503, 530, 504, 505, 518, 520, 530, 645
- Federal Specification A-A-59544 (formerly J-C-30B)
- Meets all applicable OSHA and HUD Requirements
- May be surface mounted, fished and/or embedded in plaster
- Cable Tray Rated, install per NEC®
- UL Classified 1, 2, and 3 hour through (Fire) penetration product, R14141
- Environmental Air-Handling Space Installation per NEC® 300.22(C)
- RoHS Compliant
- Made in USA of US and/or imported materials

Product Code		Trade Size	Grounding Conductor AWG	Length (ft)		Approx. Weight/ 1,000ft (lbs)	Approx. Armor O.D. (in)
Coil	Reel			Coil	Reel		
<b>MC Lite® Metal Clad Aluminum Armored Cable</b>							
<b>120/208V Solid</b>							
2107-42-00	2107-60-00	10-2 Solid (Black, White)	10 Solid (Green)	250	1000	155	0.581
2107-42-04	2107-60-04	10-2 Solid (Red, White)	10 Solid (Green)	250	1000	155	0.581
2107-42-05	2107-60-05	10-2 Solid (Blue, White)	10 Solid (Green)	250	1000	155	0.581
2108-42-00	2108-60-00	10-3 Solid (Black, Red, White)	10 Solid (Green)	250	1000	198	0.622
2108-42-04	2108-60-04	10-3 Solid (Red, Blue, White)	10 Solid (Green)	250	1000	198	0.622
2108-42-05	2108-60-05	10-3 Solid (Black, Blue, White)	10 Solid (Green)	250	1000	215	0.600
2109-42-00	2109-60-00	10-4 Solid (Black, Red, Blue, White)	10 Solid (Green)	250	1000	241	0.667
<b>120/208V Stranded</b>							
2161-42-00	2161-60-00	10-2 Stranded (Black, White)	10 Stranded (Green)	250	1000	161	0.614
2162-42-00	2162-60-00	10-3 Stranded (Black, Red, White)	10 Stranded (Green)	250	1000	289	0.659
2163-42-00	2163-60-00	10-4 Stranded (Black, Red, Blue, White)	10 Stranded (Green)	250	1000	255	0.704
<b>277/480V Solid</b>							
2107-42-01	2107-60-01	10-2 Solid (Brown, Gray)	10 Solid (Green)	250	1000	155	0.581
2107-42-02	2107-60-02	10-2 Solid (Orange, Gray)	10 Solid (Green)	250	1000	155	0.581
2107-42-03	2107-60-03	10-2 Solid (Yellow, Gray)	10 Solid (Green)	250	1000	155	0.581
2108-42-01	2108-60-01	10-3 Solid (Brown, Orange, Gray)	10 Solid (Green)	250	1000	198	0.600
2108-42-02	2108-60-02	10-3 Solid (Orange, Yellow, Gray)	10 Solid (Green)	250	1000	198	0.600
2108-42-03	2108-60-03	10-3 Solid (Brown, Yellow, Gray)	10 Solid (Green)	250	1000	198	0.600
2109-42-01	2109-60-01	10-4 Solid (Brown, Orange, Yellow, Gray)	10 Solid (Green)	250	1000	241	0.667
<b>277/480V Stranded</b>							
2161-42-01	2161-60-01	10-2 Stranded (Brown, Gray)	10 Stranded (Green)	250	1000	161	0.614
2162-42-01	2162-60-01	10-3 Stranded (Brown, Orange, Gray)	10 Stranded (Green)	250	1000	205	0.658
2163-42-01	2163-60-01	10-4 Stranded (Brown, Orange, Yellow, Gray)	10 Stranded (Green)	250	1000	255	0.704