



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MC122STBKWH 12/2 WG MC STR BK/WH/GN Alu Armor 250' *Southwire Company*

Catalog Number	MC122STBKWH
Manufacturer	Southwire Company
Description	Aluminum Armored Conductor, Stranded, 19 Strands, #12 Awg Conductor Size, PVC Jacket Material, Thermoplastic Nylon Insulation Material, Copper Conductor Material, 600 V, 20 A, Black, White and Green, 2 Conductors, 250 FT Overall Length, 0.494 In Outside Diameter, +90 °C Operating Temperature, 110 LB/MFT
Weight per unit	0.1100 (lbs/each)
Product Category	Alum Armor Copper Conductors

Features

media	Yes
-------	-----

Dimensions and Weight

Length	250
--------	-----

Descriptions

Description	12/2 WG MC STR BK/WH/GN ALU ARMOR
extra long description	SWC 69114701 Armormite Type MC

Manufacturer Information

GTIN	00032886347559
Manufacturers Part Number	2158S42-00
UPC	032886347559

Taxonomies, Classifications, and Categories

Category Description	BX & MC
Type	MC

Availability

minimum qty	250
-------------	-----

Packaging

Carton	250
Weight Per foot	0.11