

# Eaton MMX34AA023F0-0

Catalog Number: MMX34AA023F0-0

Eaton M-Max Series Adjustable Frequency Drive Full version AA software design series FS4 frame 380–480V 3-phase in 460V three-phase out IP20 enclosure rating 15 hp 23A Output current 23A Nominal AC current



Photo is representative

## General specifications

### Product Name

Eaton M-Max Series sensorless vector adjustable frequency drive

### Catalog Number

MMX34AA023F0-0

### UPC

786685626666

### Product Length/Depth

6.5 in

### Product Height

14.57 in

### Product Width

6.61 in

### Product Weight

12.5 lb

### Warranty

Eaton Selling Policy 25-000 generally applies with some exceptions. Drive products come with a standard 24 months from date of shipment and 36 months with Eaton certified start up all inclusive coverage parts labor and travel.

### Compliances

EMC Category C2, C3, and C4 (Level H): With an internal RFI filter option  
CE Marked  
RoHS Compliant  
C-Tick Compliant

### Certifications

cUL Listed  
EN 61800-5-1  
UL Listed  
IEC Rated  
EN 61800-3  
EN 60204-1

Please consult factory for extended warranty options.

## defaultTaxonomyAttributeLabel

### Horsepower

15 hp

### Phase

Three-phase

### Protection filtering

EMC Category C2 C3 and C4 (Level H) with an internal RFI filter option

### Voltage rating

380-480 V, 460 V

### Frame size

4

### Options

Full version

### Enclosure

IP20

### Output current - max

23 A

### Software

AA

### Nominal AC current

23 A

## Resources

### Brochures

[Variable frequency drive - Product overview](#)

[M-Max Series adjustable frequency drives](#)

### Catalogs

[Eaton's Volume 6—Solid-State Motor Control](#)

### Drawings

[MMX\\_\(FR4\) 2D Drawing Xchange](#)

[MMX\\_\(FR4\) 3D Inventor](#)

[MMX\\_\(FR4\) 3D Model Xchange](#)

[MMX\\_\(FR4\) AutoCAD 2D Footprint](#)

[MMX\\_\(FR4\) AutoCAD 2D Footprint \(mm\)](#)

[MMX\\_\(FR4\) 2D PDF](#)

### Installation instructions

[User Manual, M-Max Series Adjustable Frequency Drive](#)

### Specifications and datasheets

[Eaton Specification Sheet - MMX34AA023F0-0](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)