




METALLIC WIU COVERS

**Two-Gang Metal While-In-Use Covers - Extra Duty®
2-Gang 55-in-1**

C10



Catalog #: MX6200

APPLICATIONS

Designed for use whenever weatherproof protection is required while an outlet is in use.
N/A

PRODUCT FEATURES

- Heavy duty die-cast metal construction
- Patented Quick-Fit™ keyhole mounting system allows installation in under a minute.
- Pre-configured for GFCI with patented Knockout technology for alternate devices
- Includes attached gasket and mounting hardware
- Lockable tab
- Premium Powder Coat

UL LISTED

File E212332

NEMA

3R Rated

NEC

2014 Compliant (article 406.9A & B) Extra Duty Rated

US PATENTS

8,314,334

GENERAL PRODUCT INFORMATION

Color: Gray

CONFIGURATION

Gangs: 2

PRODUCT MEASUREMENTS

Depth: 3-1/2 in.
Wt. Ea. (Lbs.): 0.972

PACKAGING

Package Type:	Shrink
Std. Pkg.:	4
Product UPC-A Labeled:	Yes
Weight (Lbs. Per/C):	97.20
Ship Carton Length (in.):	14.76
Ship Carton Width (in.):	5.31
Ship Carton Height (in.):	6.69
Ctn Weight (Lbs.):	3.89
Pallet Qty:	420.00
UPC Number:	092326104838
I2of5:	40092326104836