

# Eaton NOS-100

Catalog Number: NOS-100

Eaton Bussmann series NOS fuse, Non current limiting, Light duty circuit locations, 100 A, Class H, Non-indicating, Blade end x blade end, 10 kAIC at 600 Vac, Standard, 5, 600 V

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton Bussmann series NOS fuse	NOS-100
<b>UPC</b>	<b>Product Length/Depth</b>
051712311007	7.9 in
<b>Product Height</b>	<b>Product Width</b>
1.34 in	1.34 in
<b>Product Weight</b>	<b>Warranty</b>
0.55 lb	Not Applicable
<b>Compliances</b>	
CE Marked	

## Electrical rating

### Amperage Rating

100 A

### Interrupt rating

10 kAIC at 600 Vac

### Voltage rating

600 V

## Physical details

### Packaging type

Standard

## General information

### Class

Class H

### Connection

Blade end x blade end

### Fuse indicator

Non-indicating

### Quantity

5

### Special features

Pin-indicating

## Resources

### Catalogs

[Bussmann series full line catalog 1007, section 01- low voltage branch circuit fuses](#)

[Bussmann series complete full line catalog no. 1007](#)

### Multimedia

[Bussmann series Fuseology](#)

### Specifications and datasheets

[Eaton Specification Sheet - NOS-100](#)

### Technical data sheets

[NOS-100~BUSS ONE TIME FUSE](#)

### Technical service bulletins

[Datasheet - FNQ-30](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)