



# Arlington

## Part : NMLT45125

Description: 45deg; Non-Metallic Connector

Listing: ULCSA

Country of Origin: USA

Weight: 0.245 lbs/each

Height: 2.710"

Width: 3.420"

Additional Color Options:  height="16" width="16"/>

Material(s): UV Rated Plastic

Conduit Type: Non-Metallic Liquid Tight Conduit, Type B Only

Knockout Size(s): 1-1/4"

Trade Size: 1-1/4"

## Packaging

Unit: 5 pcs

Standard: 25 pcs





# Arlington

## Part : NMLT45125

Description: 45deg; Non-Metallic Connector

Listing: ULCSA

Country of Origin: USA

Weight: 0.245 lbs/each

Height: 2.710"

Width: 3.420"

Additional Color Options:  height="16" width="16"/>

Material(s): UV Rated Plastic

Conduit Type: Non-Metallic Liquid Tight Conduit, Type B Only

Knockout Size(s): 1-1/4"

Trade Size: 1-1/4"

## Packaging

Unit: 5 pcs

Standard: 25 pcs

