



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



P832TG 4" Non-Ic Incandescent Remodel Can *Progress Lighting*

Catalog Number	P832TG
Manufacturer	Progress Lighting
Description	For Use In Existing Ceilings. Integral Flange On Housing and Exclusive Locking Bars Permits Quick Mounting On Ceilings From 1/2 In to 1 In Thick. UL and CUL Listed For Damp Locations.
Weight per unit	1.6 (lbs/each)
Product Category	Incandescent Recessed Architec

Features

Coating	unfinished
dimensions	11-3/8 W., 5-1/2 ht.
indoor/outdoor	Indoor
Lamp Type	A19
Material	Galvanized Steel
Number of Lamps	1
pallet quantity	216
Power Source	Hardwired
Socket Type	socket
Voltage Rating	120

Material, Color, and Finish

Color	Unfinished
fixture material	galvanized steel
Style	Utilitarian/Commodity

Dimensions and Weight

Height	5.5
Length	11.375
Width	4.8125

Descriptions

Description	4" NON-IC INCADESCENT REMODEL CAN
extra long description	PROG P832-TG P832-TG 4in NON-IC REM
Long Description	For use in existing ceilings. Integral flange on housing and exclusive locking bars permits quick mounting on ceilings from 1/2 in to 1 in thick. UL and CUL listed for damp locations.
Product Type	P832-TG 4IN Non-Ic Remodel Can



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	PROGRESS
GTIN	00785247104970
Manufacturers Part Number	P8367-WL28
UPC	785247104970

Taxonomies, Classifications, and Categories

Category Description	All Recessed Cans & Trims
Type	4in Remodel Housing

Trade Size

aperture size	4
---------------	---

Packaging

Carton	1
Package	6
Weight Per each	1.6

Uses, Certifications, and Standards

Mounting	CEILING
standard	UL-CUL