



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PBEL8 3" 45D Standard Elbow

Robroy/Plasti-Bond

Catalog Number	PBEL8
Manufacturer	Robroy/Plasti-Bond
Description	Factory Bent Standard Radius Elbows Are Available and Ready to Ship. Factory Bent Elbows Are More Accurate, Quicker to Install and More Economical, Because They Save Field Bending Time and Do Not Waste Materials. Electrical Continuity Is Maintained Across Assembled Joints.
Weight per unit	19.0 (lbs/each)
Product Category	Steel

Features

Connector Type	Threaded
----------------	----------

Material, Color, and Finish

Color	Gray;Red
-------	----------

Descriptions

Description	3" 45D STANDARD ELBOW
extra long description	ROB-R PRHELB-3X45 3 X 45 STANDARD E
Long Description	Factory bent standard radius elbows are available and ready to ship. Factory bent elbows are more accurate, quicker to install and more economical, because they save field bending time and do not waste materials. Electrical continuity is maintained across assembled joints.
Product Type	3 X 45 Standard Elbow
Special Features	40 mil gray PVC exterior coating - 2 mil red urethane interior coating

Manufacturer Information

Brand	ROBROY
GTIN	00784011200429
Manufacturers Part Number	PRHELB-3X45
UPC	784011200429

Taxonomies, Classifications, and Categories

Category Description	DIECAST EMT FITTINGS
Type	ELBOW

Trade Size

Trade Size	3
------------	---

Availability

Status	Inactive
--------	----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	19

Uses, Certifications, and Standards

Application	Electrical and Data wire raceways in harsh environments
standard	UL Listed, (Standard 6) File E2314 with both PVC and zinc coatings investigated as primary protection against corrosion. Restricted for use with threaded fittings only.