



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PD10NXDLA Caseta 250W Led 3WAY Light Almond

*Lutron*

Catalog Number	PD10NXDLA
Manufacturer	Lutron
Description	Caseta Wireless 3-Way/Single-Pole RF Dimmer For Led, CFL, Incandescent, Halogen, or Magnetic Low Voltage, 1000W/Va, Neutral Optional In Light Almond
Weight per unit	0.3500 (lbs/each)
Product Category	Lighting Dimmers

### Features

actuator	Push-button
connection	Wire Leads
Connection Type	Wire Leads
insulation	Plastic
Material	Plastic/Metal
media	Yes
Poles	1
Switch Type	Push button
Voltage Rating	120
Wattage	1000;1000.0000

### Material, Color, and Finish

Color	Light Almond
-------	--------------

### Dimensions and Weight

Size	4.69 x 2.94;119 x 75
------	----------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	CASETA 250W LED 3WAY LIGHT ALMOND
extra long description	LUT PD-10NXD-LA Caséta PRO 1000W Di
Features	The Lutron Caseta In-Wall Smart Dimmer Switch PRO is UL listed to work with up to 250W of dimmable LED, or 1000W Incandescent/Halogen bulbs. The Caseta Dimmer Switch PRO is also compatible with LEDs with integrated drivers, magnetic low-voltage loads, as well as Phillips Mark 10® ballasts and Lutron Hi-Lume 1% 2-Wire (LTE) LED drivers. Neutral wire connection is optional for standard LED bulbs, but required for MLV loads, LED drivers, dimmable ballasts, and power modules. Minimum load with neutral connecte
Long Description	Caseta Wireless 3-way/single-pole RF dimmer for LED, CFL, Incandescent, Halogen, or Magnetic Low Voltage, 1000W/VA, neutral optional in light almond
Product Type	Caséta Pro 1000W Dimmer Light Almond
Special Features	Controls 250 W LED (screw-base), 1000 W incandescent/halogen, 1000 VA (800 W) magnetic low-voltage, 520 W Hi-lume 1 percent 2-wire LED driver, or 5 A Tu-Wire fluorescent ballast loads. Simple, intuitive design with on, off and raise/lower buttons. Provides true dimming from each location with Pico wireless remotes. Offers reliable dimming of dimmable LEDs/CFLs, as well as halogens and incandescents

## Manufacturer Information

Brand	Lutron
GTIN	00784276146135
Manufacturers Part Number	PD-10NXD-LA
UPC	784276146135

## Taxonomies, Classifications, and Categories

Type	Wireless in-wall dimmer, multi-location/3-way/single-pole
------	---

## Packaging

Carton	3
Package	48
Weight Per each	0.35

## Uses, Certifications, and Standards

Application	Lighting Control
Enclosure	Plastic
Frequency Rating	50 to 60
Mounting	WALLBOX
Operating Temperature	32 to 104
standard	cUL, NOM, FCC, IFTEL, NEMA