



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PD10NXDWH Caseta 250W Led 3WAY White

Lutron

Catalog Number	PD10NXDWH
Manufacturer	Lutron
Description	Caseta Wireless 3-Way/Single-Pole RF Dimmer For Led, CFL, Incandescent, Halogen, or Magnetic Low Voltage, 1000W/Va, Neutral Optional In White
Weight per unit	0.3500 (lbs/each)
Product Category	Lighting Dimmers

Features

actuator	Push-button
connection	Wire Leads
Connection Type	Wire Leads
insulation	Plastic
Material	Plastic/Metal
media	Yes
Poles	1
Switch Type	Push button
Voltage Rating	120
Wattage	1000;1000.0000

Material, Color, and Finish

Color	White
-------	-------

Dimensions and Weight

Size	4.69 x 2.94;119 x 75
------	----------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	CASETA 250W LED 3WAY WHITE
extra long description	LUT PD-10NXD-WH Caséta PRO 1000W Di
Features	The Lutron Caseta In-Wall Smart Dimmer Switch PRO is UL listed to work with up to 250W of dimmable LED, or 1000W Incandescent/Halogen bulbs. The Caseta Dimmer Switch PRO is also compatible with LEDs with integrated drivers, magnetic low-voltage loads, as well as Phillips Mark 10® ballasts and Lutron Hi-Lume 1% 2-Wire (LTE) LED drivers. Neutral wire connection is optional for standard LED bulbs, but required for MLV loads, LED drivers, dimmable ballasts, and power modules. Minimum load with neutral connecte
Long Description	Caseta Wireless 3-way/single-pole RF dimmer for LED, CFL, Incandescent, Halogen, or Magnetic Low Voltage, 1000W/VA, neutral optional in white
Product Type	Caséta Pro 1000W Dimmer White
Special Features	Controls 250 W LED (screw-base), 1000 W incandescent/halogen, 1000 VA (800 W) magnetic low-voltage, 520 W Hi-lume 1 percent 2-wire LED driver, or 5 A Tu-Wire fluorescent ballast loads. Simple, intuitive design with on, off and raise/lower buttons. Provides true dimming from each location with Pico wireless remotes. Offers reliable dimming of dimmable LEDs/CFLs, as well as halogens and incandescents

Manufacturer Information

Brand	Lutron
GTIN	00784276146128
Manufacturers Part Number	PD-10NXD-WH
UPC	784276146128

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Wireless in-wall dimmer, multi-location/3-way/single-pole

Packaging

Carton	3
Package	48
Weight Per each	0.35



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Lighting Control
Enclosure	Plastic
Frequency Rating	50 to 60
Mounting	WALLBOX
Operating Temperature	32 to 104
standard	cUL, NOM, FCC, IFTEL, NEMA