

# Eaton PDG13M0015TFFJ

Catalog Number: PDG13M0015TFFJ

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 1, Three Pole, 15A, 65kA/480V, T-M (Fxd-Fxd) TU, Standard Line and Load (PDG1X3T125)

Photo is representative



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Power Defense molded case circuit breaker	PDG13M0015TFFJ
	UPC
	786679300299
<b>Product Length/Depth</b>	<b>Product Height</b>
76 mm	139.7 mm
<b>Product Width</b>	<b>Product Weight</b>
76.2 mm	1.36 kg
<b>Warranty</b>	<b>Compliances</b>
Eaton Selling Policy 25-000, one (1) year RoHS Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	<b>Certifications</b>
	CSA
	UL 489
	IEC 60947-2
	CCC Marked

## Delivery program

### Amperage Rating

15 A

### Circuit breaker frame type

Complete breaker

### Frame

1

### Number of poles

Three-pole

## General information

### Circuit breaker type

PD1 Global

### Class

Class A

### Trip Type

T-M (Fxd-Fxd) TU

## Technical data - Electrical

### Voltage rating

600 Vac

### Voltage rating - max

600 V

## Technical data - Mechanical - Terminals

### Terminals

Standard Line and Load

## Technical information

### Interrupt rating

65 kAIC at 480 Vac

### Interrupt rating range

65 kAIC @480V (UL)

25 kAIC @600V (UL/CSA)

100 kAIC Icu/ 100 kAIC Ics/ 220 kAIC Icm @240V (IEC)

70 kAIC Icu/ 50 kAIC Ics/ 154 kAIC Icm @380-415V (IEC)

100 kAIC @240V (UL)

35 kAIC Icu @250 Vdc

35 kAIC Icu @125 Vdc

## Resources

### 3D CAD drawing package

[Eaton Power Defense MCCB PDG13M0015TFFJ 3D drawing](#)

### Application notes

[Consulting application guide - molded case circuit breakers](#)

### Brochures

[Power Defense brochure](#)

[Power Defense molded case circuit breaker selection poster](#)

[Power Defense technical selling booklet](#)

[Power Defense molded case circuit breakers - Frame 1 product aid](#)

## Catalogs

Molded case circuit breakers catalog

## Certification reports

PDG1 CSA certification

PDG1 CCC certification

Power Defense Declaration concerning California's Proposition 65

EU Declaration of Conformity - Power Defense molded case circuit breakers

PDG1 UL authorization

## Installation instructions

Power Defense Frame 1-2-3-4 IP door barrier assembly instructions - IL012278EN

Power Defense Frame 1 UL Global variable depth rotary handle mech installation instructions - IL012308EN

Power Defense Frame 1 UL global interphase barrier - IL012176EN

Power Defense Frame 1 UL global box terminal (steel) 125A 3P - IL012165EN H03

Power Defense padlockable handle lock hasp top off only installation instructions - IL012226EN

Power Defense Frame 1 Instructions - IL012152EN

Power Defense Frame 1 UL global screw terminal end cap kit 125A 3P - IL012163EN

Power Defense Frame 1 UL global handle block padlockable - IL012178EN

Power Defense Frame 1 UL global interphase barrier instructions - IL012313EN

Power Defense Frame 1 UL global Padlockable Handle Lock Hasp - IL012225EN

Power Defense Frame 1 UL global DIN rail adapter three or four pole - IL012186EN

Power Defense Frame 1 UL global DIN rail adapter 2, 3, 4-pole - IL012185EN

Power Defense Frame 1 UL global screw terminal end cap kit metric 125A 3P - IL012171EN

Power Defense Frame 1 UL global DIN rail adapter metal three pole - IL012187EN

Power Defense Frame 1 UL global handle block padlockable off only - IL012179EN

Power Defense Frame 1 UL global handle block non padlockable - IL012177EN

Power Defense Frame 1 UL global tunnel terminal (aluminum) 125A 3P - IL012166EN H03

Power Defense Frame 1 UL global lock padlockable handle hasp  
IL012180EN

Power Defense Frame 1 UL global terminal shield cover IP30 3P -  
IL012174EN

#### Installation videos

Power Defense Frame 1 UL Global Aux, Alarm, ST and UVR Animated  
Instructions.rh

#### Multimedia

Power Defense Frame 3 Variable Depth Rotary Handle Mechanism  
Installation How-To Video

Power Defense Frame 5 Trip Unit How-To Video

Power Defense Frame 1 Aux, Alarm, and Shunt Trip How-To Video

Power Defense molded case circuit breakers

Power Defense Breakers

Power Defense Frame 6 Trip Unit How-To Video

Eaton Power Defense for superior arc flash safety

Power Defense Frame 2 Variable Depth Rotary Handle Mechanism  
Installation How-To Video

#### Specifications and datasheets

Eaton Specification Sheet - PDG13M0015TFFJ

#### Time/current curves

Power Defense time current curve Frame 1 - PDG1

Power Defense time current curves MCP Motor Circuit Protection – PD1,  
PD2, PD3

#### White papers

Single and double break MCCB performance revisited

Safer by design: arc energy reduction techniques

Molded case and low-voltage breaker health



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia