


ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1207 Energy Drive 75662-0000, TX Kilgore Phone: 903-984-8485 Fax: 903-984-8193





PH75MQMJFK 1PH 75VA 240X480V-120X240V 50/60HZ Cu Hammond Power Solutions

8	
Catalog Number	PH75MQMJFK
Manufacturer	Hammond Power Solutions
Description	Machine Tool Rated Molded Industrial Control Transformer,
	240X480 PV, 120X240 SV, 75 Kva, Primary and Secondary Fuse
	Clips Included
Weight per unit	3.5 (lbs/each)
Product Category	Encapsulated Industrial Contro
Features	
Wattage	75
Descriptions	
Description	1PH 75VA 240X480V-120X240V 50/60HZ CU
extra long description	HMND PH75MQMJ-FK CNTL75 VA240/480
Long Description	Machine Tool Rated Molded Industrial Control Transformer,
	240x480 PV, 120x240 SV, 75 kVA, Primary And Secondary Fuse
	Clips Included
Product Type	CNTL75 VA240/480120x240fuse
Special Features	Potted control transformer for high inrush applications powering
	coils. Options include finger safe cover and an innovative fuse
	holder system.
Manufacturer Information	
Brand	HPS Imperator®
GTIN	00803423081768
Manufacturers Part Number	PH75MQMJ-FK
UPC	803423081768
Taxonomies, Classifications, and (Categories
Category Description	
Туре	Tranformer > Dry Type > Control > Molded
Packaging	
Carton	1
Weight Per each	3.54



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1207 Energy Drive 75662-0000, TX Kilgore Phone: 903-984-8485 Fax: 903-984-8193

Uses, Certifications, and Standards

Application	Automation, Panel shops, Machines, Solenoids, Control
	Applications, Timers
Enclosure	Core and Coil
Frequency Rating	50/60
Mounting	PANEL
standard	CSA, UL, CE
Temperature Rating	Typical 30 Average/ 40 Maximum