


PLF26

High quality polycarbonate PL floodlight. Supplied with one, two or three 13 watt twin tube compact fluorescent lamps. Adjustable swivel mounting arm with 1/2" thread. Lamps supplied.

Color: Bronze

Weight: 2.6 lbs



Lamp Info

Type: 13W Twin
Watts: 26W
Shape/Size: N/A
Base: N/A
ANSI: N/A
Hours: 10,000
Lamp Lumens: 1,800
Efficacy: N/A

Ballast Info

Type: NPF 120V
120V: N/A
208V: N/A
240V: N/A
277V: N/A
Input Watts: 0W
Efficiency: N/A

Technical Specifications

UL Listing:

Suitable for wet locations. (PLF 13 & 26) For side wall mounting only.

Housing and Lens:

Corrosionproof and vandal resistant polycarbonate.

Lens Gasket:

High temperature tubular silicone.

Reflector:

Anodized aluminum.

Sockets:

GX23 base.

Lamp:

Two 13 watt compact fluorescent lamps supplied with fixture.

Minimum Temperature:

0°F .

Correlated Color Temp. (Nominal CCT):

2700K.

Patents:

RAB sensor and fixture designs are protected under U.S. and International Intellectual Property laws.

Country of Origin:

Designed by RAB in New Jersey and assembled in Taiwan.

Trade Agreements Act Compliant:

This product is a product of Taiwan and a "designated country" end product that complies with the Trade Agreements Act.

GSA Schedule:

Suitable in accordance with FAR Subpart 25.4.




PLF26

High quality polycarbonate PL floodlight. Supplied with one, two or three 13 watt twin tube compact fluorescent lamps. Adjustable swivel mounting arm with 1/2" thread. Lamps supplied.

Color: Bronze

Weight: 2.6 lbs



Lamp Info

Type: 13W Twin
Watts: 26W
Shape/Size: N/A
Base: N/A
ANSI: N/A
Hours: 10,000
Lamp Lumens: 1,800
Efficacy: N/A

Ballast Info

Type: NPF 120V
120V: N/A
208V: N/A
240V: N/A
277V: N/A
Input Watts: 0W
Efficiency: N/A

Technical Specifications

UL Listing:

Suitable for wet locations. (PLF 13 & 26) For side wall mounting only.

Housing and Lens:

Corrosionproof and vandal resistant polycarbonate.

Lens Gasket:

High temperature tubular silicone.

Reflector:

Anodized aluminum.

Sockets:

GX23 base.

Lamp:

Two 13 watt compact fluorescent lamps supplied with fixture.

Minimum Temperature:

0°F .

Correlated Color Temp. (Nominal CCT):

2700K.

Patents:

RAB sensor and fixture designs are protected under U.S. and International Intellectual Property laws.

Country of Origin:

Designed by RAB in New Jersey and assembled in Taiwan.

Trade Agreements Act Compliant:

This product is a product of Taiwan and a "designated country" end product that complies with the Trade Agreements Act.

GSA Schedule:

Suitable in accordance with FAR Subpart 25.4.

