Weight: 2.6 lbs

PLF26

High quality polycarbonate PL floodlight. Supplied with one, two or three 13 watt twin tube compact fluorescent lamps. Adjustable swivel mounting arm with 1/2" thread. Lamps supplied.

Lamp Info Ballast Info

Type:	13W Twin	Type:	NPF 120V
Watts:	26W	120V:	N/A
Shape/Size:	N/A	208V:	N/A
Base:	N/A	240V:	N/A
ANSI:	N/A	277V:	N/A
Hours:	10,000	Input Watts:	OW
Lamp Lumens:	1,800	Efficiency:	N/A
Efficacy:	N/A		

Technical Specifications

UL Listing:

Suitable for wet locations. (PLF 13 &26) For side wall mounting only.

Housing and Lens:

Corrosionproof and vandal resistant polycarbonate.

Lens Gasket:

High temperature tubular silicone.

Reflector:

Anodized aluminum.

Sockets:

GX23 base.

Lamp:

Two 13 watt compact fluorescent lamps supplied with fixture.

Minimum Temperature:

0°F.

Correlated Color Temp. (Nominal CCT):

2700K.

Patents:

RAB sensor and fixture designs are protected under U.S. and International Intellectual Property laws.


Country of Origin:

Designed by RAB in New Jersey and assembled in Taiwan.

Trade Agreements Act Compliant:

This product is a product of Taiwan and a "designated country" end product that complies with the Trade Agreements Act.

Color: Bronze



GSA Schedule:

Suitable in accordance with FAR Subpart 25.4.