



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## PLT2SM3 7.4" Org Nyl CBL Tie

*Panduit Corporation*

Catalog Number	PLT2SM3
Manufacturer	Panduit Corporation
Description	Panduit PLT2S-M3 Locking Cable Ties Are Designed to Satisfy The Needs Of Mil Spec Applications, While Delivering Consistent Performance and Reliability. Featuring A Curved Tip to Allow For Easy Pick Up From Flat Surfaces and Faster Initial Threading. Standard Cross Section, 7.4" (188MM) Length. Made Of Nylon 6.6, Are Orange In Color and Come In Packages Of 1000.
Weight per unit	0.0028 (lbs/each)
Product Category	Cable Ties & Wraps

### Features

media	Yes
Tensile Strength	50

### Dimensions and Weight

Length	7.4
Thickness	0.06
Width	NA

### Descriptions

Description	7.4" ORG NYL CBL TIE
extra long description	PAN PLT2S-M3 Pan-Ty® PLT2S-M3 Cable
Long Description	Panduit PLT2S-M3 Locking Cable Ties are designed to satisfy the needs of mil spec applications, while delivering consistent performance and reliability. Featuring a curved tip to allow for easy pick up from flat surfaces and faster initial threading. Standard cross section, 7.4" (188mm) length. Made of Nylon 6.6, are orange in color and come in packages of 1000.
Product Type	Pan-Ty® PLT2S-M3 Cable Tie, Orange, PA6.6, 7.4"L, 50LB, PK10
Special Features	Indoor

### Manufacturer Information

Brand	PANDUIT
GTIN	00074983549191
Manufacturers Part Number	PLT2S-M3
UPC	074983549191

### Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Premium Cable Tie



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Availability

minimum qty 1000

## Packaging

Carton 1

Package 5000

Weight Per each 0.0028

## Uses, Certifications, and Standards

standard CSA Certified, UL Recognized (File #E56854), UL 62275 Compliant  
(Type 2S, 21S), RoHS Compliant