



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PV3 Encl NMA12 Disc Encl *Cooper B-Line/Cable Tray*

Catalog Number	PV3
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Push Button Enclosures, 8" Height, 4.75" Length, 4" Width, Nema 12, Screw Cover, PV Enclosure, Surface Mounted, Medium Single Door, External Mounting Feet, Carbon Steel, Oil-Resistant Gasket
Weight per unit	2.5 (lbs/each)
Product Category	Control Station Enclosures

Features

dimensions	4.7500 IN X 4.0000 IN X 8.0000 IN
Material	Carbon Steel
Number of Holes	3

Material, Color, and Finish

Color	ANSI 61 GRAY
-------	--------------

Dimensions and Weight

Size	3.25 In Width X 2.75 In Depth X 8.00 In Height
------	------------------------------------------------

Descriptions

Description	ENCL NMA12 DISC ENCL
extra long description	B-LINE PV3 TYPE 12 VRTL PUSHBUTTON
Features	Eaton's B-Line series push button enclosures provide reliable environmental protection and are designed to mount standard 30.5 mm or miniature 22.5 mm oil-tight pushbuttons, pilot lights and switches
Long Description	Eaton B-Line series push button enclosures, 8" height, 4.75" length, 4" width, NEMA 12, Screw cover, PV enclosure, Surface mounted, Medium single door, External mounting feet, Carbon steel, Oil-resistant gasket
Product Type	Type 12 VRTL Pushbutton Enc
Special Features	Device Hole Size 30.5 mm

Manufacturer Information

Brand	Eaton
GTIN	00782051702446
UPC	782051702446

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Push button enclosures



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	2.5

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Mounting	Wall, Feet
nema rating	12
standard	CSA C22.2, UL 508A, NEMA