

Specifications

Photo is representative

Eaton PVML-11-J-UNV1

Eaton Crouse-Hinds series Champ Pro PVML LED fixture, Cool white, 320W HID equivalent, No guard, Glass lens, 11000 lumens, 122 lm/W, Die cast aluminum, Stanchion 25° angled, Type V, 1-1/2" trade size, 100-277 Vac, 127-250 Vdc, 92W

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series Champ Pro PVML LED light fixture
CATALOG NUMBER	PVML-11-J-UNV1
UPC	662276920101
PRODUCT LENGTH/DEPTH	15.07 in
PRODUCT HEIGHT	12.85 in
PRODUCT WIDTH	11.62 in
PRODUCT WEIGHT	22.7 lb

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC IEC
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66

Product specifications

LUMENS	11000
LUMENS PER WATT	75
COLOR TEMPERATURE	Cool white
MOUNTING METHOD	Stanchion 25° angled
TRADE SIZE	1-1/2"
OPTICAL DISTRIBUTION	Type V
GUARD TYPE	No guard
VOLTAGE RATING	100-277 Vac, 127-250 Vdc
FREQUENCY RATING	50/60 Hz
WATTAGE	92W
DIMMING	Dimmable driver
POWER FACTOR	> 0.90
EQUIVALENT LUMINAIRE	320W HID
MATERIAL	Die cast aluminum
LENS MATERIAL	Heat and impact resistant glass

Resources

3D MODELS

[SP3D Design Package - Champ Pro PVML Industrial LED Light Fixtures](#)

BROCHURES

[Crouse-Hinds series Champ Pro PVML LED Luminaires - 3,000 to 13,000 lumens brochure](#)

[Crouse-Hinds series industrial LED lighting solutions](#)

[Crouse-Hinds series Global LED lighting portfolio](#)

[Crouse-Hinds series DLC approved lighting products](#)

CATALOGS

[Crouse-Hinds series Champ Pro PVML LED luminaires - 3,000 to 13,000 lumens catalog page](#)

CERTIFICATION REPORTS

[Champ Pro PVML Industrial LED Light Fixtures Canadian certification](#)

[Champ Pro PVML Industrial LED Light Fixtures UL certification](#)

[EC Declaration of Conformity - Crouse-Hinds series Champ Pro PVML LED Luminaires](#)

INSTALLATION INSTRUCTIONS

[IF 1888 - Champ VMVL and PVML Driver Replacement](#)

[IF 1882 - Champ VMVL and PVML LED luminaires](#)

SPECIFICATIONS AND DATASHEETS

[Champ Pro PVM Industrial LED](#)

[Eaton Specification Sheet - PVML-11-J-UNV1](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications

Photo is representative

Eaton PVML-11-J-UNV1

Eaton Crouse-Hinds series Champ Pro PVML LED fixture, Cool white, 320W HID equivalent, No guard, Glass lens, 11000 lumens, 122 lm/W, Die cast aluminum, Stanchion 25° angled, Type V, 1-1/2" trade size, 100-277 Vac, 127-250 Vdc, 92W

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series Champ Pro PVML LED light fixture
CATALOG NUMBER	PVML-11-J-UNV1
UPC	662276920101
PRODUCT LENGTH/DEPTH	15.07 in
PRODUCT HEIGHT	12.85 in
PRODUCT WIDTH	11.62 in
PRODUCT WEIGHT	22.7 lb

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC IEC
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66

Product specifications

LUMENS	11000
LUMENS PER WATT	75
COLOR TEMPERATURE	Cool white
MOUNTING METHOD	Stanchion 25° angled
TRADE SIZE	1-1/2"
OPTICAL DISTRIBUTION	Type V
GUARD TYPE	No guard
VOLTAGE RATING	100-277 Vac, 127-250 Vdc
FREQUENCY RATING	50/60 Hz
WATTAGE	92W
DIMMING	Dimmable driver
POWER FACTOR	> 0.90
EQUIVALENT LUMINAIRE	320W HID
MATERIAL	Die cast aluminum
LENS MATERIAL	Heat and impact resistant glass

Resources

3D MODELS

[SP3D Design Package - Champ Pro PVML Industrial LED Light Fixtures](#)

BROCHURES

[Crouse-Hinds series Champ Pro PVML LED Luminaires - 3,000 to 13,000 lumens brochure](#)

[Crouse-Hinds series industrial LED lighting solutions](#)

[Crouse-Hinds series Global LED lighting portfolio](#)

[Crouse-Hinds series DLC approved lighting products](#)

CATALOGS

[Crouse-Hinds series Champ Pro PVML LED luminaires - 3,000 to 13,000 lumens catalog page](#)

CERTIFICATION REPORTS

[Champ Pro PVML Industrial LED Light Fixtures Canadian certification](#)

[Champ Pro PVML Industrial LED Light Fixtures UL certification](#)

[EC Declaration of Conformity - Crouse-Hinds series Champ Pro PVML LED Luminaires](#)

INSTALLATION INSTRUCTIONS

[IF 1888 - Champ VMVL and PVML Driver Replacement](#)

[IF 1882 - Champ VMVL and PVML LED luminaires](#)

SPECIFICATIONS AND DATASHEETS

[Champ Pro PVM Industrial LED](#)

[Eaton Specification Sheet - PVML-11-J-UNV1](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

