

# Eaton QB1020EP

Catalog Number: QB1020EP

Eaton QB GFCI circuit breaker,Bolt-on equipment protection,20A,10 kAIC,Single-pole,120/240V,Non-Interchangeable,30 mA Trip sensitivity,Bolt-on,#14-4 AWG,QB

General specifications



Photo is representative

|                               |                      |
|-------------------------------|----------------------|
| Product Name                  | Catalog Number       |
| Eaton QB GFCI circuit breaker | QB1020EP             |
| UPC                           | Product Length/Depth |
| 786679185995                  | 3.5 in               |
| Product Height                | Product Width        |
| 1 in                          | 3.5 in               |
| Product Weight                | Warranty             |
| 0.45 lb                       | 1 year               |
| Certifications                |                      |
| UL 489                        |                      |

## Physical Attributes

### Circuit breaker type

QB

### Connection

Bolt-on

### Mounting Method

Bolt-on

### Number of poles

Single-pole

### Type

Bolt-on equipment protection

### Wire size

#14-4 AWG

## Performance Ratings

### Amperage Rating

20 A

### Interrupt rating

10 kAIC

### Trip Type

Non-Interchangeable

### Trip rating

30 mA trip sensitivity

### Voltage rating

120/240 V

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - QB1020EP](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)