

Specifications



Eaton QBHGFT1020

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 20A, 22 kAIC, Single-pole, 120/240V, Non-Interchangeable, 5 mA Trip Sensitivity, QBHGF

General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBHGFT1020
UPC	786680131035
PRODUCT LENGTH/DEPTH	5 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	3 in
PRODUCT WEIGHT	0.4 lb
WARRANTY	1 year
CERTIFICATIONS	UL 489

Physical Attributes	
CIRCUIT BREAKER TYPE	QBHGF
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Single-pole
TYPE	Ground fault circuit breaker

Miscellaneous	
SPECIAL FEATURES	5 mA Trip Sensitivity

Performance Ratings	
AMPERAGE RATING	20 A
INTERRUPT RATING	22 kAIC
TRIP TYPE	Non-Interchangeable
TRIP RATING	5 mA trip sensitivity
VOLTAGE RATING	120/240 V

Resources	
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - QBHGFT1020

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

