

Eaton QBHW2020F

Catalog Number: QBHW2020F

Quicklag Industrial Thermal-Magnetic Circuit Breaker, 20A, QBHW type, 22 kAIC, Two-pole, Non-Interchangeable, 120/240V, Moisture-fungus treatment



Photo is representative

General specifications

Product Name	Catalog Number
Eaton QB thermal magnetic circuit breaker	QBHW2020F
	UPC
	782113534541
Product Length/Depth	Product Height
1 in	1 in
Product Width	Product Weight
1 in	1 lb
Warranty	Certifications
1 year	UL Listed
	CSA Certified
Catalog Notes	
HACR rated	

Physical Attributes

Circuit breaker type

QBHW

Mounting Method

Bolt-on

Number of poles

Two-pole

Type

Quicklag

Performance Ratings

Amperage Rating

20 A

Interrupt rating

22 kAIC

Trip Type

Non-Interchangeable

Voltage rating

120/240 V

Miscellaneous

Quantity

7

Special features

Moisture-fungus treatment

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

Specifications and datasheets

[Eaton Specification Sheet - QBHW2020F](#)

[Circuit Breaker Time/Current Curves For QUICKLAG. Industrial Circuit Breakers](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia