

Specifications



Eaton QC2030

Eaton Quicklag Type QC Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 30 A, 10 kAIC, Two-pole, 120/240 V, Thermal-magnetic, QC, Non-interchangeable

General specifications

PRODUCT NAME	Eaton QC thermal magnetic circuit breaker
CATALOG NUMBER	QC2030
UPC	786679309469
PRODUCT LENGTH/DEPTH	3.9 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	3.125 in
PRODUCT WEIGHT	0.75 lb
WARRANTY	1 year
CERTIFICATIONS	UL Listed CSA Certified

Physical Attributes

CIRCUIT BREAKER TYPE	QC
NUMBER OF POLES	Two-pole
TYPE	Industrial circuit breaker

Miscellaneous

OPTIONS	Non-interchangeable
---------	---------------------

Performance Ratings

AMPERAGE RATING	30 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	T268
VOLTAGE RATING	120/240 V

Resources

CATALOGS	Circuit Protection, Miniature Circuit Breakers and Supplementary Protectors, Volume 4, Tab 1
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - QC2030

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

