



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



QC25ERCB BK 1PH 0.25KVA 240-24 Cu Buck Booster XFMR

Hammond Power Solutions

Catalog Number	QC25ERCB
Manufacturer	Hammond Power Solutions
Description	Buck-Boost Transformer, 120X240 PV, 12X24 SV
Weight per unit	13.0 (lbs/each)
Product Category	20150804120308

Dimensions and Weight

Height	7.19
Length	5.56
Width	4.31

Descriptions

Description	BK 1PH 0.25KVA 240-24 CU BUCK BOOSTER XFMR
extra long description	HMND QC25ERCB BK 1PH 0.25KVA 240-24
Long Description	Buck-Boost Transformer, 120x240 PV, 12x24 SV
Product Type	BK 1PH 0.25KVA 240-24 Cu
Special Features	Encapsulated transformers can be used to buck and boost voltage in single and three phase applications where supply voltages are frequently above or below nominal. These transformers can also be used in low voltage transformer application.

Manufacturer Information

Brand	HPS Universal™
GTIN	00803423042479
Manufacturers Part Number	QC25ERCB
UPC	803423042479

Taxonomies, Classifications, and Categories

Category Description	BUCK & BOOST TRANSFORMERS
Type	Transformer > Dry Type > Buck-Boost

Packaging

Carton	1
Weight Per each	13



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	General purpose for raising supply voltage caused by line drop or equipment demand on the distribution system, or lower voltage caused by increased system voltages due to supply line adjustments
Enclosure	NQ1-N3R - Indoor or Outdoor
Frequency Rating	50/60
Mounting	WALL MOUNT
standard	CSA, UL, Class 1 Div II
Temperature Rating	Typical 30 Average/ 40 Maximum