QF500FW

Sleek design 500 watt Quartz flood with rounded back and fins for superior heat dissipation. Vandalproof stainless steel locking clip. Gold plated socket contacts and 250°C Teflon coated wires for extended lamp life. Lamp supplied.

Color: White

Weight: 2.8 lbs



Lamp Info **Ballast Info** N/A Type: T3 Type: 500W 120V: Watts: N/A Shape/Size: N/A 208V: N/A Base: N/A 240V: N/A ANSI: N/A 277V: N/A Hours: 2,000 Input Watts: 500W Lamp Lumens: 11,000 Efficiency: 100% Efficacy: 22 LPW

Technical Specifications

UL Listing:

Suitable for wet locations. Suitable for mounting within 1.2m (4ft) of the ground.

Housing:

Die cast aluminum, 1/2" NPS threaded arm with locking swivel fits all standard mounting covers.

Lens Gasket:

High temperature silicone gasket stays in place during relamping.

Reflector:

Semi-specular anodized aluminum.

Sockets:

Porcelain RSC base sockets with gold plated spring loaded contacts and strain relieved 250° C Teflon insulated wires.

Lens:

Thermal, tempered, shock resistant glass.

Finish:

Our environmentally friendly polyester powder coatings are formulated for high-durability and long-lasting color, and contains no VOC or toxic heavy metals.

Patents:

RAB sensor and fixture designs are protected under U.S. and International Intellectual Property laws.