

# Eaton RE85 SA

Catalog Number: RE85 SA

Eaton Crouse-Hinds series RE reducer, Rigid/IMC, End 1: 3" NPT, End 2: 1-1/2" NPT, Copper-free aluminum

## General specifications



|                                      |                      |
|--------------------------------------|----------------------|
| Product Name                         | Catalog Number       |
| Eaton Crouse-Hinds series RE reducer | RE85 SA              |
| UPC                                  | Product Length/Depth |
| 782274747033                         | 3.5 in               |
| Product Height                       | Product Width        |
| 3.5 in                               | 1.31 in              |
| Product Weight                       |                      |
| 0.73 lb                              |                      |

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

### NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

## Product specifications

### Conduit type

Rigid/IMC

### End 1 Size

3"

### End 1 Type

NPT

### End 2 Size

1-1/2"

### End 2 Type

NPT

### Material

Copper-free aluminum

## Resources

### Catalogs

[Crouse-Hinds series Explosionproof Reducers, Adapters and Plugs catalog page](#)

### Certification reports

[Explosionproof Reducers, Adapters and Plugs Canadian certification](#)

[Explosionproof Reducers, Adapters and Plugs UL certification](#)

### Specifications and datasheets

[Eaton Specification Sheet - RE85 SA](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)