

Eaton REA12 SA

Catalog Number: REA12 SA

Eaton Crouse-Hinds series REA adapter, Rigid/IMC, End 1: 1/2" NPT, End 2: 3/4" NPT, Gender end 1: male, Gender end 2: female, Copper-free aluminum

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series REA adapter	REA12 SA
UPC	Product Length/Depth
782274013220	1.75 in
Product Height	Product Width
1 in	1 in
Product Weight	
0.05 lb	

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

Product specifications

Conduit type

Rigid/IMC

End 1 Size

1/2"

End 1 Type

NPT

End 2 Size

3/4"

End 2 Type

NPT

Gender end 1

Male

Gender end 2

Female

Material

Copper-free aluminum

Resources

Catalogs

[Crouse-Hinds series Explosionproof Reducers, Adapters and Plugs catalog page](#)

Certification reports

[Explosionproof Reducers, Adapters and Plugs Canadian certification](#)

[Explosionproof Reducers, Adapters and Plugs UL certification](#)

Specifications and datasheets

[Eaton Specification Sheet - REA12 SA](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)