

# Specifications

Photo is representative

## Eaton REN-40

Eaton Bussmann series REN fuse, time lag, non current-limiting, Industrial and commercial structures, 40 A, Class H, Non-indicating, 10 kAIC, Standard, 10, 250 V

### General specifications

|                             |                                |
|-----------------------------|--------------------------------|
| <b>PRODUCT NAME</b>         | Eaton Bussmann series REN fuse |
| <b>CATALOG NUMBER</b>       | REN-40                         |
| <b>UPC</b>                  | 051712100403                   |
| <b>EAN</b>                  | 5027590182386                  |
| <b>PRODUCT LENGTH/DEPTH</b> | 0.82 in                        |
| <b>PRODUCT HEIGHT</b>       | 2.98 in                        |
| <b>PRODUCT WIDTH</b>        | 0.82 in                        |
| <b>PRODUCT WEIGHT</b>       | 0.12 lb                        |
| <b>WARRANTY</b>             | Not Applicable                 |
| <b>COMPLIANCES</b>          | Not Applicable                 |

## Electrical rating

|                         |         |
|-------------------------|---------|
| <b>AMPERAGE RATING</b>  | 40 A    |
| <b>INTERRUPT RATING</b> | 10 kAIC |
| <b>VOLTAGE RATING</b>   | 250 V   |

## General information

|                         |                                           |
|-------------------------|-------------------------------------------|
| <b>CLASS</b>            | Class H                                   |
| <b>FUSE INDICATOR</b>   | Non-indicating                            |
| <b>QUANTITY</b>         | 10                                        |
| <b>SPECIAL FEATURES</b> | Super lag, time lag, non current-limiting |

## Physical details

|                       |          |
|-----------------------|----------|
| <b>PACKAGING TYPE</b> | Standard |
|-----------------------|----------|

## Resources

|                                      |                                                                                                                               |
|--------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| <b>CATALOGS</b>                      | <a href="#">Bussmann series complete full line catalog no. 1007</a><br><a href="#">REN-40~SUPER LAG RENEWABLE FUSE 40/250</a> |
| <b>MULTIMEDIA</b>                    | <a href="#">Bussmann series Fuseology</a>                                                                                     |
| <b>SPECIFICATIONS AND DATASHEETS</b> | <a href="#">Eaton Specification Sheet - REN-40</a>                                                                            |

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

