

## Downrods - 1/2" Diameter



**Downrod Options 50/50 - Threaded on one end, smooth on the other.**

Model Number	Length	Diameter	Finish Options
<b>DR3 (Finish)</b>	<b>3"</b>	<b>1/2"</b>	<b>AB, AO, ABZ, AG, AGV, AW, BCP, BN, BR, BU, CH, DC, ESP, FB, GV, OB, PB, PT, RI, SPZ, SS, TS, W</b>
<b>DR4 (Finish)</b>	<b>4"</b>	<b>1/2"</b>	<b>AB, AG, AGV, AO, AW, BCP, BN, BU, CH, DC, ESP, GBK, OB, PB, PR, RI, SPZ, SS, TS, W</b>
<b>DR6 (Finish)</b>	<b>6"</b>	<b>1/2"</b>	<b>AB, AG, AGV, AO, AV, AW, BCP, BN, BR, BU, CH, DC, ESP, FB, GBK, GV, LB, OB, PB, PR, PT, RI, SC, SPZ, SS, TI, TS, W</b>
<b>DR8 (Finish)</b>	<b>8"</b>	<b>1/2"</b>	<b>AGV, AO, BCP, GV, OB, SPZ, TS</b>
<b>DR12 (Finish)</b>	<b>12"</b>	<b>1/2"</b>	<b>AB, ABZ, AG, AGV, AO, AV, AW, BCP, BCW, BN, BR, BU, CB, CH, DC, ESP, FB, GBK, GV, LB, MWW, OB, PB, PR, PT, RI, SPZ, SS, TI, TS, W</b>
<b>DR14 (Finish)</b>	<b>14"</b>	<b>1/2"</b>	<b>AO, BCP, PR</b>
<b>DR18 (Finish)</b>	<b>18"</b>	<b>1/2"</b>	<b>AB, ABZ, AG, AGV, AO, AV, AW, BCP, BCW, BN, BR, BU, CB, CH, DC, ESP, FB, GBK, GV, LB, MWW, OB, PB, PR, PT, RI, SPZ, SS, TI, TS, W</b>
<b>DR24 (Finish)</b>	<b>24"</b>	<b>1/2"</b>	<b>AB, ABZ, AG, AGV, AO, AV, AW, BCP, BCW, BN, BR, BU, CB, CH, DC, ESP, FB, GBK, GV, LB, MWW, OB, PB, PR, PT, RI, SC, SPZ, SS, TI, TS, W</b>
<b>DR36 (Finish)</b>	<b>36"</b>	<b>1/2"</b>	<b>AB, ABZ, AG, AGV, AO, AW, BCP, BN, BR, CH, DC, ESP, FB, GV, LB, OB, OI, PB, PR, PT, RI, SPZ, SS, TS, W</b>
<b>DR48 (Finish)</b>	<b>48"</b>	<b>1/2"</b>	<b>AB, ABZ, AG, AGV, AO, AV, AW, BCP, BCW, BN, BR, BU, CB, CH, DC, ESP, FB, GBK, GV, MWW, OB, PB, PR, PT, RI, SPZ, SS, TI, TS, W</b>
<b>DR60 (Finish)</b>	<b>60"</b>	<b>1/2"</b>	<b>AB, ABZ, AG, AGV, AO, AW, BCP, BCW, BN, BU, CB, ESP, FB, GBK, GV, MWW, OB, PB, PR, PT, RI, SPZ, SS, TI, W</b>
<b>DR72 (Finish)</b>	<b>72"</b>	<b>1/2"</b>	<b>AB, ABZ, AG, AGV, AO, AW, BCP, BCW, BN, BR, BU, CB, ESP, FB, GBK, GV, MWW, OB, PB, PR, PT, RI, SPZ, SS, TI, W</b>

## Caps



**Light Kit 1 Hole Metal Cap**

Model Finish	<b>RP-3801(Finish)</b>
Description	<b>Light Kit 1 Hole Cap, Nut &amp; Finial</b>
Finish Option	<b>AB, ABZ, AG, AO, AW, BN, BNK, BR, BU, FB, GV, OB, PB, PR, PT, RI, RT, W</b>



**Light Kit 1 Hole Glass Cap**

Model-Finish	Finish Option
<b>RP-3810-1</b>	<b>Alabaster Swirl</b>
<b>RP-3811-1</b>	<b>Clear (Shown)</b>
<b>RP-3812-1</b>	<b>Frosted</b>
<b>RP-3813-1</b>	<b>Frosted Opal</b>
<b>RP-3814-1</b>	<b>Sandstone</b>
<b>RP-3815-1</b>	<b>Tea-Stained</b>



**Light Kit 2 Hole Metal Cap**

Model Finish	<b>RP-3802(Finish)</b>
Finish Option	<b>AB, ABZ, AG, AO, AW, BN, BNK, BR, BS, BU, FB, GV, OB, PB, PR, PT, RI, RT, W</b>



**Light Kit 2 Hole Glass Cap**

Model-Finish	Finish Option
<b>RP-3810-2</b>	<b>Alabaster Swirl</b>
<b>RP-3811-2</b>	<b>Clear (Shown)</b>
<b>RP-3812-2</b>	<b>Frosted</b>
<b>RP-3813-2</b>	<b>Frosted Opal</b>
<b>RP-3814-2</b>	<b>Sandstone</b>
<b>RP-3815-2</b>	<b>Tea-Stained</b>