Specifications



Photo is representative





Eaton S10N06A82N

Eaton General purpose encapsulated transformer, buck-boost general-purpose encapsulated transformer, EP, aluminum, NEMA 3R, 54, 60 Hz, single-phase, 120 V, 240 V, 16/32 V, NONE, 115 °C rise, 0.1 KVA, indoor-outdoor, 3C

General specifications	
PRODUCT NAME	Eaton General purpose encapsulated transformer
CATALOG NUMBER	S10N06A82N
UPC	786680383168
PRODUCT LENGTH/DEPTH	4 in
PRODUCT HEIGHT	8.91 in
PRODUCT WIDTH	4.11 in
PRODUCT WEIGHT	8 lb
WARRANTY	Eaton Selling Policy 25- 000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed
CATALOG NOTES	Model N
PRODUCT TYPE	Encapsulated transformer



Physical Attributes	
COIL MATERIAL	Aluminum
DESIGN	EP
ENCLOSURE	NEMA 3R
FRAME	54
TAP SIZE	None
ТҮРЕ	Buck-Boost General- Purpose Encapsulated Transformer
WIRING CONNECTION	3C

Performance Ratings		
FREQUENCY RATING	60 Hz	
PHASE	Single-phase	
PRIMARY VOLTAGE	120 V, 240 V	
SECONDARY VOLTAGE	16/32 V	
TEMPERATURE RISE	115 °C rise	
VOLT AMPERE RATING	0.1 kVA	

Miscellaneous	
WEATHERSHIELD	Indoor-Outdoor

Resources	
CATALOGS	Commercial Distribution, Transformers, Volume 2, Tab 2
SPECIFICATIONS AND DATASHEETS	<u>Eaton Specification Sheet - S10N06A82N</u>
WARRANTY GUIDES	Selling Policy 25-000 - Distribution and Control Products and Services

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.









