



4 INCH ROUND CEILING BOX

S120JFAN | [Pass & Seymour](#)

FEATURES & BENEFITS

Ceiling Fan Box, Premium Grade with integral fan mounting bracket and four Auto/Clamps. 12 pack.



- Constructed of impact-resistant Noryl thermoplastic, making it virtually unbreakable and non-conductive.
- Auto Clamp cable clamps molded in, hold wire securely in box.
- UL Listed for fan and fixture support.
- Large, 20.25 cubic inch capacity for extra wiring space.
- Depth-mounting gauge at bottom of bracket helps you align the box at the proper depth relative to the ceiling.
- Angled, rugged, metal mounting bracket safely and securely fastens fans or fixtures to the building structure.
- Dual mounting accepts fans or fixtures with 2.75 inch or 3.5 inch straps.
- Fan mounts directly to bracket through box with #10-32 screws (provided).
- Phillips-head screws (#10-32 x 3 inch) mount the fan or fixture directly to the metal bracket.
- Ringed nails for tighter grip.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Size: 4"

Type: Ceiling Box

Special Features: Round

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: No
CUL Listing No: No
cULus: No
cURus: No
Federal Spec: No
UL Listing No: Yes
UN SPSC: 39121308
UR: No

DIMENSIONS

Depth (US): 2.1875
Diameter (US): 4
Volume: 20.25

TECHNICAL INFORMATION

Material: Plastic
Mounting: Auto Clamps
Shape: round

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA
Buy American Act Status: Buy American Act Compliant





4 INCH ROUND CEILING BOX

S120JFAN | [Pass & Seymour](#)

FEATURES & BENEFITS

Ceiling Fan Box, Premium Grade with integral fan mounting bracket and four Auto/Clamps. 12 pack.



- Constructed of impact-resistant Noryl thermoplastic, making it virtually unbreakable and non-conductive.
- Auto Clamp cable clamps molded in, hold wire securely in box.
- UL Listed for fan and fixture support.
- Large, 20.25 cubic inch capacity for extra wiring space.
- Depth-mounting gauge at bottom of bracket helps you align the box at the proper depth relative to the ceiling.
- Angled, rugged, metal mounting bracket safely and securely fastens fans or fixtures to the building structure.
- Dual mounting accepts fans or fixtures with 2.75 inch or 3.5 inch straps.
- Fan mounts directly to bracket through box with #10-32 screws (provided).
- Phillips-head screws (#10-32 x 3 inch) mount the fan or fixture directly to the metal bracket.
- Ringed nails for tighter grip.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Size: 4"

Type: Ceiling Box

Special Features: Round

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: No
CUL Listing No: No
cULus: No
cURus: No
Federal Spec: No
UL Listing No: Yes
UN SPSC: 39121308
UR: No

DIMENSIONS

Depth (US): 2.1875
Diameter (US): 4
Volume: 20.25

TECHNICAL INFORMATION

Material: Plastic
Mounting: Auto Clamps
Shape: round

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA
Buy American Act Status: Buy American Act Compliant

