



S4169

1500T3Q/CL

1500 watt; Halogen; T3; Clear; 1500 Average rated Hours;
32000 Lumens; Double Ended base; 120 volts



Features

- Bright, Crisp light
- UV-Filter halogen capsule
- Uniform light output

S4169

Item Number		UPC		Watts	Voltage	Lamp Shape	Base	ANSI Base	Lamp Code
S4169		045923041693		1500	120	T3	Double Ended	R7s	1500T3Q/CL
Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Kelvin Temp	Color	Average Rated Hours		
Clear	10-1/16"	0.38"	C-8	32000	2900	Warm White	1500		
Pack		Package Type		Dimmable/Non-Dimmable			RoHS Compliant		
480/12		Box		Dimmable			Yes		



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S4169

1500T3Q/CL

1500 watt; Halogen; T3; Clear; 1500 Average rated Hours;
32000 Lumens; Double Ended base; 120 volts



Features

- Bright, Crisp light
- UV-Filter halogen capsule
- Uniform light output

S4169

Item Number	UPC	Watts	Voltage	Lamp Shape	Base	ANSI Base	Lamp Code
S4169	045923041693	1500	120	T3	Double Ended	R7s	1500T3Q/CL
Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Kelvin Temp	Color	Average Rated Hours
Clear	10-1/16"	0.38"	C-8	32000	2900	Warm White	1500
Pack	Package Type	Dimmable/Non-Dimmable				RoHS Compliant	
480/12	Box	Dimmable				Yes	



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

