

Project Name

Location

Prepared By



Notes

[www] 06-09-2021 01:41:24

General

Status	Active
Watts	15W
Shape	T8
Base	Medium Bi Pin
ANSI Base	G13
Nominal Length	18
Finish	Gloss White
CCT (Kelvin)	4100
Temperature	Cool White
CRI	62
Lumens	850L
Beam Spread	360
Hours Rated	7500
Lamp Type	Linear
Technology	Fluorescent

Electrical

Hg Content	3.5
Operating Temperature	Ballast Dependent

Physical

MOL	17.78
MOD	1

Additional Information

Warranty	Avg. Rated Hour Limited
----------	-------------------------

Compliance

Safety Listing	Not Listed
Location Rating	Dry
Energy Star	No
California Status	Lawful for sale
RoHS Compliant	Yes
SDS Sheet	Linear_Fluorescent_Lamp