



# S9544

3JC/G6.35/LED/3000K/12V/D  
3 watt; JC LED; 3000K; G6.35 base; 12 volts

### Features

- Solid State LED lighting
- High Efficacy
- Long life
- Dimmable

Silicon LED Replacements for Halogen G6.35 lamps.



S9544

| Item Number   | UPC            | Voltage             | Watts                        | Base       | Lamp Code                 | Dimmable/Non-Dimmable | Finish |
|---------------|----------------|---------------------|------------------------------|------------|---------------------------|-----------------------|--------|
| S9544         | 045923095443   | 12                  | 3                            | G6.35      | 3JC/G6.35/LED/3000K/12V/D | Dimmable              | Clear  |
| MOL In Inches | Initial Lumens | Average Rated Hours | Kelvin Temp                  | Color      | CRI                       | Beam Spread Deg       | Pack   |
| 1 5/8"        | 300            | 25000               | 3000                         | Warm White | 80                        | 360                   | 200/20 |
| Package Type  | RoHS Compliant | UL or ETL Listed    | UL Classification            |            |                           |                       |        |
| Box           | Yes            | Yes                 | cETLus - Damp Location Rated |            |                           |                       |        |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S9544

3JC/G6.35/LED/3000K/12V/D  
3 watt; JC LED; 3000K; G6.35 base; 12 volts

### Features

- Solid State LED lighting
- High Efficacy
- Long life
- Dimmable

Silicon LED Replacements for Halogen G6.35 lamps.



S9544

| Item Number   | UPC            | Voltage             | Watts                        | Base       | Lamp Code                 | Dimmable/Non-Dimmable | Finish |
|---------------|----------------|---------------------|------------------------------|------------|---------------------------|-----------------------|--------|
| S9544         | 045923095443   | 12                  | 3                            | G6.35      | 3JC/G6.35/LED/3000K/12V/D | Dimmable              | Clear  |
| MOL In Inches | Initial Lumens | Average Rated Hours | Kelvin Temp                  | Color      | CRI                       | Beam Spread Deg       | Pack   |
| 1 5/8"        | 300            | 25000               | 3000                         | Warm White | 80                        | 360                   | 200/20 |
| Package Type  | RoHS Compliant | UL or ETL Listed    | UL Classification            |            |                           |                       |        |
| Box           | Yes            | Yes                 | cETLus - Damp Location Rated |            |                           |                       |        |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

