

Project Name

Location

Prepared By



SATCO S9827

4.5G25/SW/LED/E26/27K/120V

Notes

[www] 06-27-2021 00:19:14

General

Status	Active
Watts	4.5W
Incandescent Equivalent	40W
Volts	120V
Shape	G25
Base	Medium
ANSI Base	E26
Finish	Soft White
CCT (Kelvin)	2700
Temperature	Warm White
CRI	80
Lumens	420L
Beam Spread	360
Dimmable	Yes-Dimmable
Hours Rated	15000
Lamp Type	Globe
Technology	LED

Electrical

Operating Frequency	60 Hz
Dimming Type	Reverse Phase
Power Factor	0.9
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	4.38
MOD	3.13
Weight (lb.)	0.09

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	Yes
ES Unique ID	ESID-2308486
California Status	Non-Compliant
California Compliant Substitute	S9619
RoHS Compliant	Yes
SDS Sheet	LED_Lamp