

# S9923 CA11 LED

3.5W CFC/LED/27K/CL/120V

Lamp Type	LED
Bulb Type	CA11
Base Type	E12
Wattage	3.5
Color Temperature	2700
Color Rendering Index CRI	80
Warranty	3 Year Limited



## Lighting Facts Per Bulb

**Brightness** 350 lumens

**Estimated Energy Cost** \$0.36

per year, based on 3 hrs/day, 11c/kWh.  
Energy cost depends on utility rates and light use.

**Average Life** 13.7 years

Based on 3 hrs/day

## Light Appearance



**Energy Used** 3 watts

## Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S9923	LED	*20045923099230	120	3.5	40	CA11	Candelabra
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
E12	3.5W CFC/LED/27K/CL/120V	Yes	n/a	4 11/16	1 3/8	350	15000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
2700	Warm White	80	360	24	Box	n/a	Yes

# S9923 CA11 LED

3.5W CFC/LED/27K/CL/120V

Lamp Type	LED
Bulb Type	CA11
Base Type	E12
Wattage	3.5
Color Temperature	2700
Color Rendering Index CRI	80
Warranty	3 Year Limited



## Lighting Facts Per Bulb

**Brightness** 350 lumens

**Estimated Energy Cost** \$0.36

per year, based on 3 hrs/day, 11c/kWh.  
Energy cost depends on utility rates and light use.

**Average Life** 13.7 years

Based on 3 hrs/day

## Light Appearance



**Energy Used** 3 watts

## Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S9923	LED	*20045923099230	120	3.5	40	CA11	Candelabra
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
E12	3.5W CFC/LED/27K/CL/120V	Yes	n/a	4 11/16	1 3/8	350	15000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
2700	Warm White	80	360	24	Box	n/a	Yes