



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **SBC20Q Split Bolt Conn** *Panduit Corporation*

Catalog Number	SBC20Q
Manufacturer	Panduit Corporation
Description	Split Bolt Connector, #2 Awg (Stranded) Conductor Size, #2/0 Awg (Stranded) Conductor Size, Non-Insulated, Copper Conductor Material, 1.72 In Overall Length
Weight per unit	1.0 (lbs/each)
Product Category	Large Terminals & Connectors

### **Features**

Material	Copper
media	Yes
Voltage Rating	600 V

### **Material, Color, and Finish**

Finish	blank
--------	-------

### **Descriptions**

Also Known As...	Kearnys Split Bolt Connector Monkey balls Bug
Description	SPLIT BOLT CONN
extra long description	PAN SBC2/0-Q Pan-Lug™ SBC2/0-Q Mech
similar brands	Servit®

### **Manufacturer Information**

Brand	PANDUIT
GTIN	00074983627264
UPC	074983627264

### **Taxonomies, Classifications, and Categories**

Category Description	SPLIT BOLTS
Type	Mechanical Split Bolt Connector

### **Packaging**

Carton	1
Package	25
Weight Per each	1

### **Uses, Certifications, and Standards**

standard	UL listed to 467 and 486 and CSA certified for use up to 600V & Temperature Rated to 90°C
----------	---