Industrial LED luminaires

Exit and Emergency

Sure-Lites







SEL/SELM Indoor/Outdoor

WAREHOUSE / DISTRIBUTION | MANUFACTURING | GYMNASIUMS / MULTI-PURPOSE ROOMS / ATHLETIC CENTER | BIG BOX / RETAIL



Polycarbonate





Feature	Benefit
Up to 60 feet of egress coverage	Up to \$300 savings on installation
LED source with Nickel cadmium battery	Up to ten years with no maintenance
Optional remote capacity	Indoor, outdoor design flexibility
Self-diagnostics w/laser test	Reduce labor of NFPA/OSHA testing


!	CC to 40°C C
SEL60, SELM60	©
←	—— 60 ft. ———

Certification/warranty	
UL924 damp location	
NFPA 101 compliant	
NEC/OSHA compliant	
5-year product warranty	
7-year prorated battery warranty	











SELHP100R3 Indoor

WAREHOUSE / DISTRIBUTION | MANUFACTURING | GYMNASIUMS / MULTI-PURPOSE ROOMS / ATHLETIC CENTER | BIG BOX / RETAIL

SELHP100R3/SELHP100R3SD



Feature	Benefit
Up to 100 feet of egress coverage	Fewer fixtures required for egress coverage
LED source with LiFePO ₄ battery	Peace of mind
3 Watts remote capacity	Indoor, outdoor design flexibility
Self-diagnostics option	Reduce labor of NFPA/OSHA testing



Certification/warranty	
UL924 damp location	
NFPA 101 compliant	
NEC/OSHA compliant	
5-year product warranty	
5-year battery warranty	










SELW/SELD Outdoor

WAREHOUSE / DISTRIBUTION | MANUFACTURING | GYMNASIUMS / MULTI-PURPOSE ROOMS / ATHLETIC CENTER | BIG BOX / RETAIL



Feature	Benefit
LED source with Nickel cadmium battery	Up to ten years with no maintenance
Forward throw optic	Maximum design flexibility
29 feet spacing	Less fixtures required
Self-diagnostics w/laser test	Reduce labor of NFPA/OSHA testing

Certification/warranty	
UL924 wet location	
NFPA 101 compliant	
NEC/OSHA compliant	
5-year product warranty	
7-year prorated battery warranty	













Feature	Benefit
LED source with Nickel cadmium battery	Up to ten years with no maintenance
58 foot spacing	Less fixtures required
Standard self-diagnostics with laser test	Reduce labor of NFPA/ OSHA testing
NEMA 4X; IP66; - 30° C to 50° C	Maximum design flexibility

Certification	
UL924 wet location	
NEMA 4X	
NFPA 101 compliant	
NEC/OSHA compliant	
IP66	← 60 ft. —
NSF	
IP66HAZ (class 1, Div 2) option	












WAREHOUSE / DISTRIBUTION | MANUFACTURING | GYMNASIUMS / MULTI-PURPOSE ROOMS / ATHLETIC CENTER | BIG BOX / RETAIL

LPX Exit





Feature	Benefit
LED source with Nickel cadmium battery	Up to ten years with no maintenance
Field adjustable for red or green	Maximum design flexibility
Optional emergency heads or remote capacity	Less fixtures required
Standard self-diagnostics with laser test	Reduce labor of NFPA/OSHA testing



Certification/warranty	
UL924 damp location	
NFPA 101 compliant	
NEC/OSHA compliant	
5-year product warranty	
7-year prorated battery warranty	










LPX LED Combo









LPWX Outdoor

WAREHOUSE / DISTRIBUTION | MANUFACTURING | GYMNASIUMS / MULTI-PURPOSE ROOMS / ATHLETIC CENTER | BIG BOX / RETAIL







Feature	Benefit
LED source with Nickel cadmium battery	Up to ten years with no maintenance
Field adjustable for red or green	Maximum design flexibility
Standard self-diagnostics with laser test	Reduce labor of NFPA/OSHA testing
NEMA 4X; IP66; - 30° C to 50° C	Maximum design flexibility

Certification/warranty		
UL924 wet location		
NEMA 4X/IP66		
NFPA 101 compliant		
NEC/OSHA/NSF compliant		
HAZ (class 1, Div 2) rated option		
NSF		
5-year product warranty, 7-year prorated battery warranty		









LPWX Exit			
)	
12-13/32"	[315mm] —		
Garage			
	1/2" — mm]	4-13/32" – [112mm]	_
		[2 8-11/32 [212mm	n]
		□ γ □ Y=2-1/2 [63mm	z" 1]
6 -5-1	1/2"	[112mm] [2] 8-11/32 [212mm] Y=2-1/2	233mm] " n] 2"

Feature	Benefit
LED source with Nickel cadmium battery	Up to ten years with no maintenance
UV stabilized polycarbonate housing	Outdoor capable
Standard self-diagnostics with laser test	Reduce labor of NFPA/OSHA testing
Wet location listed; - 30° C to 50° C	Maximum design flexibility

Certification/warranty
UL924 wet location
NFPA 101 compliant
NEC/OSHA compliant
5-year product warranty, 7-year prorated battery warranty









Why Sure-Lites?

Product Features



EZ Key External Battery Disconnect

• Prevents the battery from cycling during the construction phase and ensures a full battery charge for inspection.





Laser Test

• Enables remote testing by utilizing a laser pointer to simulate AC power loss and engagement of emergency operation.



Self-diagnostics

• Eliminates labor intensive NFPA required monthly testing.



Red/Green Selectable

- Easy for distribution/no call backs.
- LPX, LPXC, CX and UX series.

LPX Exit







CX Exit



UX Exit



Lighting Brands

Ametrix AtLite Corelite **Ephesus** Fail-Safe HALO

HALO Commercial

Invue iΟ Iris Lumark Lumière McGraw-Edison

Metalux MWS Neo-Ray Portfolio

PrentaLux - 3D Printed Lighting

RSA Shaper Streetworks Sure-Lites Telensa

Controls Brands

Greengate Fifth Light

Intelligent Lighting Controls

Connected Lighting Systems and Smart Spaces Platform

WaveLinx



Cooper Lighting Solutions 1121 Highway 74 South Peachtree City, GA 30269 P: 770-486-4800 www.cooperlighting.com

Canada Sales Sanaud Sales 5925 McLaughlin Road Mississauga, Ontario L5R 1B8 P: 905-501-3000 F: 905-501-3172



