



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SGB386CL 2" Diecast Mighty-Right Split Ground Bushing *Bridgeport Fittings*

Catalog Number	SGB386CL
Manufacturer	Bridgeport Fittings
Description	Insulating Bushing, Straight Connection Orientation, 0.29 LB/Ea
Weight per unit	0.2930 (lbs/each)
Product Category	Aluminum

Features

Material	Zinc Alloy
media	Yes

Material, Color, and Finish

Color	Grey with Black Insulator
Finish	Ball burnish

Dimensions and Weight

Size	2
------	---

Descriptions

Description	2" DIECAST MIGHTY-RIGHT SPLIT GROUND BUSHING
extra long description	BPT SGB-386CL 2" SPLT GND BSH W/LUG
Features	Split Bushings install after the wire pull. No more burning through bushings or fighting with pullers. Save time and effort too!
Special Features	Grounding Lug Wire Capacity # 4 - #1/0

Manufacturer Information

GTIN	00781747903860
UPC	781747903860

Taxonomies, Classifications, and Categories

Category Description	Locknuts, Bushings, Re-Bushings, Re-Washers, Threaded Plugs, Knockout Plugs
Type	SPLIT

Trade Size

Trade Size	2
------------	---

Packaging

Carton	10
Package	100
Weight Per each	0.293



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Used in situations where wires have already been pulled through Rigid/IMC conduit, and an insulated bushing is required. Grounding lug; aluminum alloy 6061-T6. Rated 150 Degree C. cULus listed. Patented. Now featuring UV Stabilized Insulators and Stainless Steel Hardware, perfect for solar and other outdoor installations!

standard

cULus

Temperature Rating

150°C