



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SP14 Vinylink 16-14 Splice

Burndy LLC

Catalog Number	SP14
Manufacturer	Burndy LLC
Description	Copper Splice, 16-14 Awg, 1" Splice Length, Vinyl Insulated.
Weight per unit	0.0030 (lbs/each)
Product Category	Small Terminals & Connectors

Features

insulation	Y
Insulation Type	Vinyl
Material	Copper
pallet quantity	99999

Material, Color, and Finish

Color Code	BLUE
------------	------

Descriptions

Description	VINYLINK 16-14 SPLICE
extra long description	BUR SP14 SPLICE- 16- 14 AWG-VINYL
Long Description	Copper Splice, 16-14 AWG, 1" Splice Length, Vinyl Insulated.
Product Type	Splice
Special Features	Features: The Type SP VINYLINK Is A PVC Insulated Seamless Butt Splice, Type SP VINYLINK Is Designed To Accommodate A Broad Range Of 600 Volt Cables, Manufactured From Seamless Electrolytic Copper Tubing: Provides Maximum Conductivity And Tensile Strength, In A High Quality Design With NO Seams To Split, Funnel Entry: Provides Easy Wire Insertion, Electro-Tin Plated: Provides Durable Long Lasting Resistance To Corrosion, Expanded Insulation Support: Lower Inventory Requirements, Red Wire Range Of 22-16: Lo

Manufacturer Information

Brand	BURNDY
GTIN	00781810712016
Manufacturers Part Number	SP14
sub brand	VINYLINK
UPC	781810712016

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	SP



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton 50

Weight Per each 0.003

Uses, Certifications, and Standards

Application For Accommodating A Broad Range Of 600 Volt Cables

Temperature Rating 105° C