

Features

- Ideal for highly corrosive environments
- Non-magnetic
- Protective plastic film helps to prevent scratches and damage
- 1-Single 1.40 in. (35.6) Diameter Opening

Ordering Information

Description	Catalog Number	UPC
1-Gang, 1-Single Receptacle Opening, 1.40" (35.6) Dia. Hole	SS7	883778201103



Listings

UL Listed
CSA Certified

Specifications

Plate Material	Stainless steel 302/304
Plate Type	Wall Plate
Plate Openings	Single Receptacle
Mounting Screws	302/304 SS, Slotted Head
Appearance	Horizontal brushed finish

Online Resources

eCatalog

Features

- Ideal for highly corrosive environments
- Non-magnetic
- Protective plastic film helps to prevent scratches and damage
- 1-Single 1.40 in. (35.6) Diameter Opening

Ordering Information

Description	Catalog Number	UPC
1-Gang, 1-Single Receptacle Opening, 1.40" (35.6) Dia. Hole	SS7	883778201103



Listings

UL Listed
CSA Certified

Specifications

Plate Material	Stainless steel 302/304
Plate Type	Wall Plate
Plate Openings	Single Receptacle
Mounting Screws	302/304 SS, Slotted Head
Appearance	Horizontal brushed finish

Online Resources

[eCatalog](#)