

Eaton STL131A120CH

Catalog Number: STL131A120CH

Eaton meter socket, Transformer rated socket, 20A, Under, Solid top, 13-jaw, Pre-wired test switch, 600 Vac

General specifications



Photo is representative

Product Name	Catalog Number
Eaton meter socket	STL131A120CH
UPC	Product Length/Depth
786685703404	5.3 in
Product Height	Product Width
21.8 in	12.6 in
Product Weight	Warranty
26 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	Catalog Notes
UL Listed	Austin Energy Approved, tranformer rated

Type

Transformer rated socket

Amperage Rating

20A

Feed type

Bottom

Number of jaws

13-jaw

Voltage rating

600 V

Accessories

Pre-wired test switch

Number of sockets

1

Drawings

[Dimensional Drawing - SKT/SW 20A 13T FW ST](#)

Specifications and datasheets

[Eaton Specification Sheet - STL131A120CH](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.
All other trademarks are property of their respective owners.



Eaton.com/socialmedia